

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
APPLICABLE STANDARD											
RATING	OPERATING TEMPERATURE RANGE		-55℃ TO +85℃(note1)			STORAGE TEMPERATURE RANGE		-10℃ TO +60℃			
	VOLTAGE		30 V AC/DC			APPLICABLE CONNECTOR		BM23FR0.6-50DS-0.35V(**)			
	CURRENT		0.3A								
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS			QT	AT	
CONSTRUCTION											
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.			X	X	
MARKING		CONFIRMED VISUALLY.							X	X	
ELECTRICAL CHARACTERISTICS											
CONTACT RESISTANCE		20mV AC OR LESS 1kHz, 1mA				100mΩ MAX			X	-	
INSULATION RESISTANCE		100V DC				50MΩ MIN			X	-	
VOLTAGE PROOF		100V AC FOR 1min.				NO FLASHOVER OR BREAKDOWN			X	-	
MECHANICAL CHARACTERISTICS											
MECHANICAL OPERATION		10 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: 100mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.			X	-	
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
SHOCK		490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
ENVIRONMENTAL CHARACTERISTICS											
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)				① CONTACT RESISTANCE: 100mΩ MAX ② INSULATION RESISTANCE: 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2℃, 90 TO 95%, 96h.				① CONTACT RESISTANCE: 100mΩ MAX ② INSULATION RESISTANCE: 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)				① CONTACT RESISTANCE: 100mΩ MAX			X	-	
DRAWING FOR REFERENCE This is subjet to change without notice											
REMARKS Note 1 ; INCLUDE THE TEMPERATURE RISING BY CURRENT.					DRAWN S.H.JUNG 17.05.08	DESIGNED S.H.JUNG 17.05.08	CHECKED H.W.JO 17.05.08	APPROVED T.S.KANG 17.05.08	RELEASED ENG 17.05.08 DEPT		
Unless otherwise specified, refer to JIS C 5402 and IEC 60512											
Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET				PART NO. BM23FR0.6-50DP-0.35V(895)				
CODE NO.(OLD) CL		DRAWING NO. SLC4-632214			CODE NO. CL 6644-0085-7-895					1 1	