

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-40°C TO + 85°C (NOTE 1) 	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C		
	OPERATING HUMIDITY RANGE	40% TO + 80% (NOTE 2)	STORAGE HUMIDITY RANGE	40% TO + 70%		
	VOLTAGE	250V AC	APPLICABLE CONNECTOR	DF11-*DS-2C		
	CURRENT	0.5A	APPLICABLE CABLE	UL1061/UL1007 AWG30		
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		100mA (DC OR 1000 Hz).		30mΩ MAX.	X	—
MECHANICAL CHARACTERISTICS						
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
CONTACT INSERTION AND EXTRACTION FORCE		□0.5±0.002 BY STEEL GAUGE.		INSERTION FORCE 4.4N MAX EXTRACTION FORCE 0.3N MIN	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS						
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35 °C TIME 30→10 TO 15→30→10 TO 15 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.		① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
REMARKS						
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT						
NOTE 2:NO CONDENSING.						
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	1	DIS-H-008540	MI. SAKIMURA	HK. UMEHARA	14. 02. 26	
Unless otherwise specifid , refer to IEC 60512.				APPROVED	TS. SAKATA	09. 11. 17
				CHECKED	TS. FUKUSHIMA	09. 11. 17
				DESIGNED	TH. YOSHI ZAWA	09. 11. 16
				DRAWN	TH. YOSHI ZAWA	09. 11. 16
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-081092-01	
	SPECIFICATION SHEET		PART NO.	DF11-30SCFA (04)		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL543-0607-6-04		1/1