

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)	
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)	
	CURRENT	0.5 A (note 1)	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.			x	x
ELECTRICAL CHARACTERISTICS					
CONTACT RESISTANCE	1mA(DC OR 1000Hz).		50 mΩ MAX. INCLUDING FPC,FFC BULK RESISTANCE (L=8mm)	x	x
INSULATION RESISTANCE	100 V DC.		500 MΩ MIN.	x	x
VOLTAGE PROOF	150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	x	x
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	x	—
SHOCK	981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
FPC RETENTION FORCE	MEASURED BY APPLICABLE FPC. (CONNECTOR,FPC AT INITIAL CONDITION. THICKNESS OF FPC SHALL BE t=0.30mm)		DIRECTION OF INSERTION: 0.4xn N MIN (n : NUMBER OF CONTACTS)	x	—
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40→+15T ₀ +35→+85→+15T ₀ +35°C TIME 30→ 2 TO 3 → 30→ 2 TO 3 min. UNDER 5 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.			x	—
DAMP HEAT,CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
DRY HEAT	EXPOSED AT 85±2 °C, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX.	x	—
COLD	EXPOSED AT -40±3°C, 96 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
CORROSION SALT MIST	EXPOSED AT 35±2 °C 5% SALT WATER SPLAY FOR 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	x	—
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 25±5 ppm FOR 96 h.			x	—
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.			x	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	0				
REMARK			APPROVED	NF. MIYAZAKI	15. 12. 09
			CHECKED	SJ. OKAMURA	15. 12. 09
			DESIGNED	SG. MASAKI	15. 12. 09
Unless otherwise specified, refer to IEC 60512.			DRAWN	RN. IIDA	15. 10. 20
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-156279-55-00
HRS	SPECIFICATION SHEET		PART NO.	FH12-**S-1SH (55)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL586	△ 1/2

Jun.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (TO BE 2 TIMES MAX.) PEAK TMP. 250 °C MAX REFLOW TMP. OVER 230°C WITHIN 60 sec. PRE-HEATING. 150 TO 200°C 90 TO 120 sec. 2)SOLDERING IRONS : 350 ± 10 °C, FOR 5± 1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235±5 °C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	×	—

(note 1)

WHEN THE SAME VALUE OF CURRENT ARE APPLID TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC-156279-55-00	
HRS	SPECIFICATION SHEET		PART NO.	FH12-**S-1SH (55)	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL586	△ 2/2