

Jan.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)	STORAGE TEMPERATURE RANGE	-10°C TO +60 °C(NOTE3)	
	OPERATING HUMIDITY RANGE	40% TO 80%(NOTE2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTE3)	
	VOLTAGE	AC 150 V	APPLICABLE CONNECTOR	DF13-4S-1.25C	
	CURRENT	1 A	APPLICABLE CRIMP CONTACT	DF13-2630SCFA, DF13-3032SCFA	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20mV MAX, 1mA (DC OR 1000Hz).	30 mΩ MAX.	X	-	
INSULATION RESISTANCE	100 V DC.	500 MΩ MIN.	X	-	
VOLTAGE PROOF	500 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-	
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		X	-	
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 →5 TO 35 →+85→5 TO35°C TIME 30 →10 TO 15 →30 →10 TO 15min UNDER 5 CYCLES.		X	-	
RESISTANCE TO SOLDERING HEAT	(1) REFLOW SOLDERING 《REFLOW AREA》 MAX 250°C WITHIN 10 sec. 230°C MIN WITHIN 60 sec. 《PREHEATING AREA》 170°C to 190 °C 60 sec TO 120 sec. PUT THROUGH IN REFLOW FURNACE TWICE. LEAVE IN AMBIENT TEMPERATURE AND HUMIDITY FOR 1 HOUR. CONNECTOR TEMPERATURE TO BE AMBIENT FOR SECOND REFLOW. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE 350°C, FOR 5 sec. NO STRENGTH ON CONTACT.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	-	
SOLDERABILITY	SOLDERING TEMPERATURE : 300°C DURATION OF IMMERSION : SOLDERING, FOR 3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	X	-	
REMARKS					
NOTE1: INCLUDING THE TEMPERATURE RISE BY CURRENT. NOTE2:NO CONDENSING. NOTE3:APPLY TO THE CONDITION OF LONGTERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
Unless otherwise specified, refer to JIS C 5402.			APPROVED	TS. SAKATA	08.12.11
			CHECKED	TS. KUMAZAWA	08.12.10
			DESIGNED	SN. KOBAYASHI	08.12.10
			DRAWN	SN. KOBAYASHI	08.12.10
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-083412-01
	SPECIFICATION SHEET		PART NO.	DF13C-4P-1.25V (51)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL536-0403-8-51	1/1