

Dec.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO 85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO 60°C	
	VOLTAGE	50V AC	APPLICABLE CONNECTOR	DF17# (**)-40DS-0.5V (57)	
	CURRENT	0.3A			
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).	60mΩ MAX.	X	—	
INSULATION RESISTANCE	100V DC.	500MΩ MIN.	X	—	
VOLTAGE PROOF	150V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—	
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	① INSERTION FORCE :40.0 (N)MAX ② WITHDRAWAL FORCE :4.0(N)MIN	X	—	
MECHANICAL OPERATION	50TIMES INSERTIONS AND WITHDRAWALS.	① CONTACT RESISTANCE: 60mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35°C TIME 30→10 TO 15→ 30→10TO15min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 250 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—	
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	—	
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JEIDA-39)	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	—	
HEAT RESISTANCE OF SOLDERING	【RECOMMENDED TEMPERATURE PROFILE】 《SOLDERING AREA》 MAX250°C, 220°C FOR 60 SECONDS MAX. 《PREHEATING AREA》 150 TO 180°C 90~120 SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. 【RECOMMENDED MANUAL SOLDELING CONDITION】 SOLDERING IRON TEMPERATURE 350°C SOLDERING TIME : WITHIN 3 SECONDS.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS			APPROVED	KH. IKEDA	08.09.26
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT.			CHECKED	TS. MIYAZAKI	08.09.26
UNLESS OTHERWISE SPECIFIED,REFER TO JIS C 5402.			DESIGNED	TY. YAMASAKI	08.09.04
			DRAWN	TY. YAMASAKI	08.09.04
Note	QT:Qualification Test	AT:Assurance Test	X:Applicable Test	DRAWING NO.	ELC4-161718-04
	SPECIFICATION SHEET		PART NO.	DF17 (2.0)-40DP-0.5V (57)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL683-0084-7-57	△ 1/1

FORM HD0011-2-1