Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO + 60°C
	VOLTAGE	50V AC	APPLICABLE CONNECTOR	DF17#(**)-*DP-0.5V(**)
	CURRENT	0.3A		

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100m A (DC OR 1000 Hz).	60mΩ MAX.	X	—
INSULATION RESISTANCE	100V DC.	500MΩ MIN.	X	—
VOLTAGE PROOF	150V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	SIGNAL / INSERTION FORCE (N)MAX / WITHDRAWAL FORCE (N)MIN: 20 / 20.0 / 2.0; 26 / 26.0 / 2.6; 30 / 30.0 / 3.0; 40 / 40.0 / 4.0; 50 / 50.0 / 5.0; 60 / 60.0 / 6.0; 70 / 70.0 / 7.0; 80 / 80.0 / 8.0; 100 / 100.0 / 10.0; 120 / 120.0 / 12.0	X	—
MECHANICAL OPERATION	50TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 60mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK	490 m/s^2 DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 5 TO 35→ 85→ 5 TO 35°C TIME 30→10 TO 15→ 30→10TO15min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 60mΩ MAX. ② INSULATION RESISTANCE: 250 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	—
SULPHUR DIOXIDE	EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JEIDA-39)	① CONTACT RESISTANCE: 60 mΩ MAX. ② NO HEAVY CORROSION.	X	—
⚠1 HEAT RESISTANCE OF SOLDERING	【RECOMMENDED TEMPERATURE PROFILE】 《SOLDERING AREA》 MAX250℃, 220℃ FOR 60 SECONDS MAX. 《PREHEATING AREA》 150 TO 180℃ 90～120 SECONDS. MAXIMUM TWICE ACTION IS ALLOWED UNDER THE SAME CONDITION. 【RECOMMENDED MANUAL SOLDELING CONDITION 】 SOLDERING IRON TEMPERATURE 350℃ SOLDERING TIME : WITHIN 3 SECONDS.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
⚠1	1	DIS-H-000664	HK.MURAKAMI	TS.MIYAZAKI	05.12.06

REMARKS
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT.

UNLESS OTHERWISE SPECIFIED,REFER TO JIS C 5402.

APPROVED	MO.NAKAMURA	05.04.01
CHECKED	TS.MIYAZAKI	05.03.31
DESIGNED	YH.MICHIDA	05.03.31
DRAWN	YH.MICHIDA	05.03.31

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-162127-04

SPECIFICATION SHEET		PART NO.	DF17(3.0)-*DS-0.5V(57)	
HIROSE ELECTRIC CO., LTD.		CODE NO.	CL683 ⚠1	1/1

FORM HD0011-2-1