

Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD			
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 85 °C	STORAGE TEMPERATURE RANGE -10°C TO 50°C (PACKED CONDITION)
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE RELATIVE HUMIDITY 90% MAX (NOT DEWED)
	CURRENT	※ 0.5 A	APPLICABLE CABLE t=0.3±0.05 , GOLD PLATED

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	
MARKING	CONFIRMED VISUALLY.		×	×

ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	1 mA (DC OR 1000 Hz).	50 mΩ MAX. INCLUDING FPC, FFC BULK RESISTANCE (L=8mm)	×	×
INSULATION RESISTANCE	100 V DC.	500 MΩ MIN.	×	×
VOLTAGE PROOF	150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×

MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, FOR 10 CYCLES IN 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	×	—
SHOCK	981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
FPC RETENSION FORCE	MEASURED BY APPLICABLE FPC. (CONNECTOR, FPC AT INITIAL CONDITION. THICKNESS OF FPC SHALL BE t=0.30mm)	DIRECTION OF INSERTION : 0.4 × n N MIN. (n : NUMBER OF CONTACTS)	×	—

ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40 → +15 to +35 → +85 → +15 to +35 °C TIME 30 → 2 to 3 → 30 → 2 to 3 min. UNDER 5 CYCLES.	① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.		×	—
DAMP HEAT, CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES, TOTAL 240 h.	① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DRY HEAT	EXPOSED AT 85 ± 2 °C, 96 h.	① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
COLD	EXPOSED AT -40 ± 3 °C, 96 h.		×	—

EMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Unless otherwise specified, refer to JIS C 5402.	D.YAMADA 04.03.25	T.MURAI 04.03.25	R. Takayanagi 04.03.26	M. Ishida 04.03.26	

Note QT: Qualification Test AT: Assurance Test ×: Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO. FH12A - * * S - 0.5SH (55)
--------------------------------------	---------------------	--

CODE NO. (OLD) CL	DRAWING NO. ELC4 - 150722 - 51	CODE NO. CL 586	1 2
----------------------	-----------------------------------	--------------------	--------



Jul.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CORROSION SALT MIST	EXPOSED AT 35±2 °C, 5 % SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×	—
SURPHUR DIOXIDE [JIS C 0090]	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 80±5 % , 25±5 PPM FOR 96 h.		×	—
HYDROGEN SULPHIDE [JIS C 0092]	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 80±5 % , 10 TO 15 PPM FOR 96 h.		×	—
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (TO BE 2 TIMES MAX.) PEAK TMP. 250 °C MAX. REFLOW TMP. 230 °C MIN. FOR 30 sec. PRE-HEATING. 150 TO 200 °C 90 TO 120 sec. 2) SOLDERING IRONS : 350 ± 10 °C, FOR 5±1 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235 ± 5 °C, FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—

※ WHEN THE SAME VALUE OF CURRENT ARE APPLID TO ALL CONTACTS AT THE SAME TIME IN ONCE,
 SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Unless otherwise specified, refer to JIS C 5402.	D.YAMADA	T.MURAI	<i>R. Takayama</i>	<i>M. Ishida</i>	
	04.03.25	04.03.25	04.03.25	04.03.26	

Note QT:Qualification Test AT:Assurance Test ×:Applicable Test

HRS HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET	PART NO. FH12A - * * S - 0.5SH (55)
CODE NO.(OLD) CL	DRAWING NO. ELC4 - 150722 - 51	CODE NO. CL 586
		2

TO
NC

