

Jun.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTE 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C	
	VOLTAGE	100 V AC	APPLICABLE CONNECTOR	DF19#-30P-1H(56)	
	CURRENT	0.5 A			
<b>SPECIFICATIONS</b>					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
<b>CONSTRUCTION</b>					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	<input type="radio"/>	<input type="radio"/>
MARKING	CONFIRMED VISUALLY.			<input type="radio"/>	<input type="radio"/>
<b>ELECTRIC CHARACTERISTICS</b>					
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).		50 mΩ MAX.	<input type="radio"/>	-
INSULATION RESISTANCE	100 V DC.		500 MΩ MIN.	<input type="radio"/>	-
VOLTAGE PROOF	300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	<input type="radio"/>	-
<b>MECHANICAL CHARACTERISTICS</b>					
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	<input type="radio"/>	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	<input type="radio"/>	-
SHOCK	490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			<input type="radio"/>	-
<b>ENVIRONMENTAL CHARACTERISTICS</b>					
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→-5 TO 35→+85 →-5 TO 35 °C TIME 30→2 TO 3 → 30 →2 TO 3 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 50mΩ MAX. ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	<input type="radio"/>	-
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.			<input type="radio"/>	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
<input type="checkbox"/>					
REMARKS			APPROVED	TY. OMA	06.03.16
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT.			CHECKED	HK. UMEHARA	06.03.16
Unless otherwise specified, refer to JIS C 5402.			DESIGNED	IO. DENPOUYA	06.03.16
			DRAWN	AK. MIURA	06.03.14
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-163241-03		
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	DF19G-30S-1F (05)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL685-0033-9-05	<input type="checkbox"/> 1/1