

APPLICABLE STANDARD					
RATING	VOLTAGE	250 V AC	CURRENT	3 A	
	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)	STORAGE TEMPERATURE RANGE	-10°C TO +60 °C	
	APPLICABLE CONNECTOR	DF1B-*DS-2.5RC			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA(DC OR 1000HZ).	30 mΩ MAX.	X	—
INSULATION RESISTANCE		500 V DC.	1000 MΩ MIN.	X	—
VOLTAGE PROOF		650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
SHOCK		490 m/s <sup>2</sup> DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 →5 TO 35 →+85→5 TO35°C TIME 30 →10 TO 15 →30 →10 TO 15min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② INSULATION RESISTANCE: 1000 MΩ MIN. ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, 250±5°C, FOR, IMMERSION, DURATION, 5s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 230±5°C FOR INSERTION DURATION, 3s.	SOLDER SHALL COVER MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS NOTE1: INCLUDING THE TEMPERATURE RISE BY CURRENT.  Unless otherwise specified, refer to JIS C 5402.			APPROVED	TY. OMA	06. 02. 20
			CHECKED	HK. UMEHARA	06. 02. 20
			DESIGNED	IO. DENPOUYA	06. 02. 20
			DRAWN	AK. MIURA	06. 02. 15
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-071801-03
HRS	SPECIFICATION SHEET		PART NO.	DF1B-*DP-2. 5DS (01)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541	△ 1/1