

APPLICABLE STANDARD					
RATING	VOLTAGE	250 V AC (DC)	CURRENT	3 A	
	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60 °C(NOTE 3)	
	OPERATING HUMIDITY RANGE	40% TO + 80%(NOTE 2)	STORAGE HUMIDITY RANGE	40% TO + 70%(NOTE 3)	
	APPLICABLE CABLE	UL1007,1061 : 20-22 AWG	APPLICABLE CONNECTOR	DF1E-*S-2.5C	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD		20 mV MAX, 1mA (DC OR 1000Hz).	30 mΩ MAX.	X	-
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND EXTRACTION FORCE		□0.635±0.002mm BY STEEL GAUGE.	INSERTION FORCE : 4.4 N MAX. EXTRACTION FORCE : 0.29 N MIN.	x	-
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			
ENVIRONMENTAL CHARACTERISTICS					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→5 TO 35→+85→5 TO35 °C TIME 30 →5 →30 →5 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	① CONTACT RESISTANCE: 30 mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.	X	-
REMARKS					
NOTE 1:INCLUDING THE TEMPERATURE RISE BY CURRENT					
NOTE 2:NO CONDENSING.					
NOTE 3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATINGTEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION.					
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
Unless otherwise specified, refer to JIS C 5402.			APPROVED	KI. AKIYAMA	12. 10. 11
			CHECKED	HK. UMEHARA	12. 10. 11
			DESIGNED	HT. SATO	12. 10. 11
			DRAWN	MI. SAKIMURA	12. 10. 10
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-162826-01
HRS	SPECIFICATION SHEET		PART NO.	DF1E-2022SCFA	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL541-1001-5-00	△ 1/1