Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD		△1		
RATING	OPERATING TEMPERATURE RANGE	-40°C TO 105°C(***note1***)	STORAGE TEMPERATURE RANGE	−10 °C TO 50 °C (PACKED CONDITION)
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)
	CURRENT	0.5 A (***note2***)	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING (GND PLATE: t=0.5±0.05mm, TIN PLATING)

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRICAL CHARACTERISTICS				
VOLTAGE PROOF	150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×
INSULATION RESISTANCE	100 V DC.	500 MΩ MIN.	×	×
CONTACT RESISTANCE	AC 20 mV MAX (1 KHz) , 1 mA .	100 mΩ MAX. INCLUDING FFC BULK RESISTANCE (L=8mm)	×	×
MECHANICAL CHARACTERISTICS				
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, − m/s^2 FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 100 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SHOCK	981 m/s^2 , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.			
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
FFC RETENTION FORCE	MEASURED BY APPLICABLE FPC. (THICKNESS OF FFC SHALL BE t=0.30mm AT INITIAL CONDITION.)	DIRECTION OF INSERTION: 0.3N × n MIN.	×	—
ENVIRONMENTAL CHARACTERISTICS				
RAPID CHANGE OF TEMPERATURE △1	TEMPERATURE-40→+15TO+35→+105→+15TO+35°C TIME 30→ 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2°C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.		×	—
DAMP HEAT,CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
DRY HEAT △1	EXPOSED AT 105±2 °C, 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
COLD	EXPOSED AT -40±3°C, 96 h.		×	—

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△1	7	DIS-F-00001058	HK. KINOUCHI	HS. SAKAMOTO	16.02.02

REMARK

Unless otherwise specified, refer to IEC 60512. △1

APPROVED	MO. ISHIDA	09.07.07
CHECKED	YN. TAKASHITA	09.07.07
DESIGNED	YK. OTSUKA	09.07.07
DRAWN	YK. OTSUKA	09.07.07

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-325208-00

HRS	SPECIFICATION SHEET	PART NO.	FH41-**S-0.5SH(05)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL580 △1	1/2

FORM HD0011-2-1

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CORROSION SALT MIST	EXPOSED AT 35±2°C , 5 % SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SULPHUR DIOXIDE △1 [JIS C 60068-2-42]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% ,25±5 ppm FOR 96 h.		×	—
HYDROGEN SULPHIDE △1 [JIS C 60068-2-43]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% ,10 TO 15 ppm FOR 96 h.		×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±5 °C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING PEAK TMP. 250 °C MAX . REFLOW TMP. OVER 230 °C WITHIN 60 sec. 2) SOLDERING IRONS : TMP. 350±10°C FOR 5±1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—

△1 (***note1***)

FOLLOW THE SPECIFICATIONS OF FFC IF IT'S ALLOWABLE MAXIMUM OPERATING TEMPERATURE IS BELOW 105℃.

(***note2***)

WHEN THE SAME VALUE OF CURRENT ARE APPLID TO ALL CONTACTS AT THE SAME TIME IN ONCE,
SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.