

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾
	VOLTAGE	50 V AC		OPERATING HUMIDITY RANGE	95 % RH MAX. (NO DEW CONDENSATION IS PERMITTED)
	CURRENT	0.3 A			
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×
MARKING		CONFIRMED VISUALLY.			×
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).		60 mΩ MAX.	×
INSULATION RESISTANCES		100 V DC		100 MΩ MIN.	×
VOLTAGE PROOF		150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	×
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCE		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE: 72 N MAX. WITHDRAWAL FORCE: 4.8 N MIN.	×
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 70 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE : 0.75 mm, AT 10 CYCLES FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			×
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 ± 2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 70 mΩ MAX. ② INSULATION RESISTANCE: 100 MΩ MIN.	×
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +15 ~ +35 → +85 → +15 ~ +35 °C TIME 30 → 2 ~ 3 → 30 → 2 ~ 3 min. UNDER 5 CYCLES.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
DRY HEAT		EXPOSED AT 85 °C, 96 h.		① CONTACT RESISTANCE: 70 mΩ MAX.	×
COLD		EXPOSED AT -55 °C, 96 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		NO HEAVY CORROSION.	×
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS C 0090)		① CONTACT RESISTANCE: 70 mΩ MAX. ② NO HEAVY CORROSION.	×
RESISTANCE TO SOLDERING HEAT		1) REFLOW SOLDERING : 250 °C MAX, : 220 °C MIN, FOR 60 s 2) SOLDERING IRONS : 360 °C, FOR 5 s		NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT.	×
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 240 ± 3 °C, FOR IMMERSION DURATION, 3 s.		A NEW UNIFORM COATING OF SOLDER SHALL OVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	×
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK ⁽¹⁾ TEMPERATURE RISE INCLUDED WHEN ENERGIZED. ⁽²⁾ THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.			APPROVED	HS.OKAWA	06.04.26
			CHECKED	HS.OZAWA	06.04.25
			DESIGNED	KY.NAKAMURA	06.04.25
Unless otherwise specified, refer to JIS C 5402.			DRAWN	KY.NAKAMURA	06.04.25
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-152109-25
HRS	SPECIFICATION SHEET		PART NO.	FX11LA-80S/8-SV (71)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL573-0103-4-71	△ 1/1