

Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 85 °C ⁽¹⁾			OPERATING HUMIDITY RANGE	40 % TO 80 %			
	VOLTAGE	100 V AC			APPLICABLE CABLE (AWG SIZE)	AWG 30 TO 32			
	CURRENT	0.5 A			APPLICABLE CABLE (OUTER DIAMETER)	φ 0.5 TO 0.6 mm			
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			×	×
MARKING		CONFIRMED VISUALLY.						×	×
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		20 mV MAX. 1 mA (DC OR 1000Hz)			60 mΩ MAX. ⁽²⁾			×	
MECHANICAL CHARACTERISTICS									
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.			① CONTACT RESISTANCE: 80 mΩ MAX. ⁽²⁾ ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS			×	
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE : 1.5 mm, AT 2 h FOR 3 DIRECTION.			① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			×	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.						×	
PULL FORCE STRENGTH (CRIMP STRENGTH)		ONLY COREWIRE IS CRIMPED AND MEASURED.			AWG 30 : 8 N MIN. AWG 32 : 5 N MIN.			×	
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.			① CONTACT RESISTANCE: 80 mΩ MAX. ⁽²⁾ ② INSULATION RESISTANCE: 500 MΩ MIN.			×	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+15~+35→+85→+15~+35°C TIME 30 → 2~3 → 30 → 2~3 min UNDER 5 CYCLES.			③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			×	
CORROSION SALT MIST		EXPOSED IN 5% SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			×	
SULFUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS-C-0090)						×	
REMARKS ⁽¹⁾ INCLUDE TEMPERATURE RISE OF CURRENT CARRYING. ⁽²⁾ INCLUDE CONDUCTOR RESISTANCE OF CABLE ASSEMBLED. (L=12mm)									
				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				<i>K. Shibusawa</i>	<i>K. Shibusawa</i>	<i>H. Yamaguchi</i>	<i>H. Okawa</i>		
				05.02.01	05.02.01	05.02.01	05.02.01		
Unless otherwise specified, refer to JIS C 5402.									
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test									
HS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO.		
							FX15-3032PCFA		
CODE NO.(OLD)			DRAWING NO.			CODE NO.			1
CL			ELC4 - 155324			CL 575-2001-8			1

