


APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾		
	VOLTAGE	100 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %		
	CURRENT	0.5 A		STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾		
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		×	×
MARKING		CONFIRMED VISUALLY.				×	×
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE		20 mV MAX, 1 mA(DC OR 1000Hz)		60 mΩ MAX. ⁽³⁾		×	
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.		×	
VOLTAGE PROOF		300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		×	
MECHANICAL CHARACTERISTICS							
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE: 24.6 N MAX. WITHDRAWAL FORCE: 2.05 N MIN.		×	
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGL AMPLITUDE : 0.76 mm, AT 2 h FOR 3 DIRECTION.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				×	
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.		×	
DRY HEAT		EXPOSED AT 85±2 °C, 96 h					
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+5~+35→+85→+5~+35°C TIME 30→ 5 MAX→ 30→ 5 MAX min. UNDER 5 CYCLES.				×	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② NO HEAVY CORROSION.		×	
SULFUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD: JIS-C-0090)				×	
RESISTANCE TO SOLDERING HEAT		1)REFLOW SOLDERING : REFLOW 2 TIMES UNDER THE TEMPERATURE PROFILE SHOWN BELOW.  2) SOLDERING IRONS : 360°C MAX. FOR 5 sec.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.		×	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE 240±3°C FOR IMMERSION DURATION, 3 sec.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.		×	
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
							
REMARKS ⁽¹⁾ INCLUDE TEMPRERATURE RISE CAUSED BY CURRENT-CARRYING. ⁽²⁾ "STORAGE" MEANS A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE ASSEMBLY TO PCB. ⁽³⁾ INCLUDE CONDUCTOR RESISTANCE OF CABLE IN CASE THE MATED CONNECTOR IS CABLE TYPE.(L=12mm) Unless otherwise specified, refer to JIS-C-5402.				APPROVED	HS. OKAWA	05. 08. 05	
				CHECKED	HT. YAMAGUCHI	05. 08. 05	
				DESIGNED	KN. SHIBUYA	05. 08. 05	
				DRAWN	KN. SHIBUYA	05. 08. 05	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-155937-00	
	SPECIFICATION SHEET			PART NO.	FX15S-41S-0. 5SH		
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL575-2307-8-00  1/1		