


APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	100 V AC		OPERATING HUMIDITY RANGE	40 % TO 80 %	
	CURRENT	0.5 A		STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT AT	
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x x	
MARKING		CONFIRMED VISUALLY.			x x	
ELECTRIC CHARACTERISTICS						
CONTACT RESISTANCE		20 mV MAX, 1 mA(DC OR 1000Hz)		60 mΩ MAX. ⁽³⁾	x	
INSULATION RESISTANCE		100 V DC.		500 MΩ MIN.	x	
VOLTAGE PROOF		300 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	x	
MECHANICAL CHARACTERISTICS						
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE: 30.6 N MAX. WITHDRAWAL FORCE: 2.55 N MIN.	x	
MECHANICAL OPERATION		50 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGL AMPLITUDE : 0.75 mm, FOR 2 h IN 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms FOR 3 TIMES IN 3 DIRECTIONS.			x	
ENVIRONMENTAL CHARACTERISTICS						
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② INSULATION RESISTANCE: 500 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	
DRY HEAT		EXPOSED AT 85±2 °C, 96 h			x	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+5~+35→+85→+5~+35°C TIME 30→ 5 MAX→ 30→ 5 MAX min. UNDER 5 CYCLES.			x	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		① CONTACT RESISTANCE: 80 mΩ MAX. ⁽³⁾ ② NO HEAVY CORROSION.	x	
SULFUR DIOXIDE		EXPOSED IN 25 PPM FOR 96 h. (TEST STANDARD: JIS C 60068)			x	
RESISTANCE TO SOLDERING HEAT		1)REFLOW SOLDERING : REFLOW 2 TIMES UNDER THE TEMPERATURE PROFILE SHOWN BELOW.  2) SOLDERING IRONS : 360°C MAX. FOR 5 sec.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.		x
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE 240±3°C FOR IMMERSION DURATION, 3 sec.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
△						
REMARKS ⁽¹⁾ INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. ⁽²⁾ "STORAGE" MEANS A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE ASSEMBLY TO PCB. ⁽³⁾ INCLUDE CONDUCTOR RESISTANCE OF CABLE IN CASE THE MATED CONNECTOR IS CABLE TYPE. (L=12mm) Unless otherwise specified, refer to JIS-C-5402.			APPROVED	HS. OKAWA	07. 07. 26	
			CHECKED	EJ. WAKATSUKI	07. 07. 26	
			DESIGNED	TH. NODA	07. 07. 25	
			DRAWN	TH. NODA	07. 07. 25	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-156704-00	
HS	SPECIFICATION SHEET		PART NO.	FX15SC-51S-0.5SH		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL575-2311-5-00	△ 1/1	