







Mar. 1. 2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

| APPLICABLE STANDARD  |  |  |                           |                                |   |
|--|--|--|---------------------------|--------------------------------|---|
| <br><b>RATING</b> | OPERATING TEMPERATURE RANGE  | -55 °C TO 85 °C <sup>(1)(2)</sup>  | STORAGE TEMPERATURE RANGE | -10 °C TO 60 °C <sup>(3)</sup> |   |
|  | VOLTAGE  | 60 V AC <sup>(5)</sup>   | OPERATING HUMIDITY RANGE  | RH 85 % MAX <sup>(2)(4)</sup>  |   |
|  | CURRENT  | 0.5 A <sup>(5)</sup>   | STORAGE HUMIDITY RANGE    | RH 70 % MAX <sup>(3)(4)</sup>  |   |
|  | APPLICABLE CABLE   | AWG 36,40 THIN COAXIAL CABLE / FFC <sup>(6)</sup>  |                           |                                |   |
| SPECIFICATIONS   |  |  |                           |                                |   |
| ITEM   | TEST METHOD  | REQUIREMENTS   | QT                        | AT                             |   |
| <b>CONSTRUCTION</b>  |  |  |                           |                                |   |
| GENERAL EXAMINATION  | VISUALLY AND BY MEASURING INSTRUMENT.  | ACCORDING TO DRAWING.  | x                         | x                              |   |
| MARKING  | CONFIRMED VISUALLY.  |  | x                         | x                              |   |
| <b>ELECTRIC CHARACTERISTICS</b>  |  |  |                           |                                |   |
| CONTACT RESISTANCE   | 20 mV MAX, 1 mA(DC OR 1000Hz)  | 80mΩ MAX. <sup>(7)</sup>   | x                         |                                |   |
| INSULATION RESISTANCE  | 100 V DC.  | 500 MΩ MIN.  | x                         |                                |   |
| VOLTAGE PROOF  | 200 V AC FOR 1 min.  | NO FLASHOVER OR BREAKDOWN.   | x                         |                                |   |
| <b>MECHANICAL CHARACTERISTICS</b>  |  |  |                           |                                |   |
| INSERTION AND WITHDRAWAL FORCES  | MEASURED BY APPLICABLE CONNECTOR.  | INSERTION FORCE: 15.5 N MAX.<br>WITHDRAWAL FORCE: 1.55 N MIN.  | x                         |                                |   |
| MECHANICAL OPERATION   | 50 TIMES INSERTIONS AND EXTRACTIONS.   | ① CONTACT RESISTANCE: NO VARIATION OF 20 mΩ OR MORE FROM INITIAL VALUE.<br>② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.                            | x                         |                                |   |
| VIBRATION  | FREQUENCY 10 TO 55 Hz,<br>SINGL AMPLITUDE : 0.75 mm,<br>AT 2 h FOR 3 DIRECTION.  | ① NO ELECTRICAL DISCONTINUITY OF 1 μs.<br>② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.   | x                         |                                |   |
| SHOCK  | 490 m/s <sup>2</sup> , DURATION OF PULSE 11 ms<br>AT 3 TIMES FOR 3 DIRECTIONS.   |  | x                         |                                |   |
| LOCK STRENGTH  | MATE TO APPLICABLE CONNECTOR AND APPLY PULL FORCE HORIZONTALLY.  | 30 N MIN.  | x                         |                                |   |
| <b>ENVIRONMENTAL CHARACTERISTICS</b>   |  |  |                           |                                |   |
| DAMP HEAT (STEADY STATE)   | EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.   | ① CONTACT RESISTANCE: NO VARIATION OF 20 mΩ OR MORE FROM INITIAL VALUE.  | x                         |                                |   |
| DRY HEAT   | EXPOSED AT 85±2 °C, 96 h   |  |                           |                                |   |
| RAPID CHANGE OF TEMPERATURE  | TEMPERATURE -55→+5~+35→+85→+5~+35°C<br>TIME 30→ 5 MAX→ 30→5 MAX min.<br>UNDER 5 CYCLES.  | ② INSULATION RESISTANCE: 500 MΩ MIN.<br>③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.   | x                         |                                |   |
| CORROSION SALT MIST  | EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.  | ① CONTACT RESISTANCE:NO VARIATION OF 20 mΩ OR MORE FROM INITIAL VALUE.<br>② NO DEFECT SUCH AS CORROSION WHICH IMPAIRS THE FUNCTION OF CONNECTOR. | x                         |                                |   |
| SULFUR DIOXIDE   | EXPOSED IN 25 PPM FOR 96 h.<br>(TEST STANDARD: JIS C 60068)  |  |                           |                                |   |
| RESISTANCE TO SOLDERING HEAT   | 1)SOLDERING HEAT WELDER :<br>PRESSURIZATION:15±2N<br>(COAXIAL CABLE) HEATING Y:275±5°C, X:2±0.5 sec<br>(FFC) HEATING Y:265±5°C, X:2.5±0.5 sec<br><br><br>2) SOLDERING IRONS : 360°C MAX. FOR 3 sec.   | NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.   | x                         |                                |   |
| SOLDERABILITY  | SOLDERED AT SOLDER TEMPERATURE 240±3°C FOR IMMERSION DURATION, 3 sec.  | A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.   | x                         |                                |   |
|  | COUNT  | DESCRIPTION OF REVISIONS   | DESIGNED                  | CHECKED                        | DATE  |
|                 | 2  | DIS-F-004353   | KN. SHIBUYA               | HT. YAMAGUCHI                  | 09. 12. 15  |
|                 | <b>REMARKS</b> (1) INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING.<br>(2) OPERATING TEMPERATURE SHOULD BE -55 TO 40°C WHEN HUMIDITY EXCEEDS 80% RH.<br>(3) THE SPECIFICATION IS APPLIED TO THE PRE-ASSEMBLED COMPONENT AND THE CABLE ASSEMBLED PRODUCT BOTH IN DELIVERY AND STORAGE, BEFORE ASSEMBLED TO PCB.<br>(4) THERE MUST NOT BE DEWFALL.<br>(5) IT IS THE MAXIMUM VALUE OF CONNECTOR. CONFIRM THE SPECIFICATION OF THE CABLE.<br>(6) ONLY FFC THAT PROCESSES THE TERMINAL THAT WE SPECIFIED.<br>(7) DON'T INCLUDE CONDUCTOR RESISTANCE OF CABLE.<br><br>Unless otherwise specified, refer to JIS-C-5402. |  | APPROVED                  | HS. OKAWA                      | 08. 05. 24  |
|  |  |  | CHECKED                   | HT. YAMAGUCHI                  | 08. 05. 24  |
|  |  |  | DESIGNED                  | TS. SHIBUYA                    | 08. 05. 24  |
|  |  |  | DRAWN                     | TS. SHIBUYA                    | 08. 05. 24  |
| Note   | QT:Qualification Test AT:Assurance Test X:Applicable Test  |  | DRAWING NO.               | ELC4-158270-00                 |   |
|                 | SPECIFICATION SHEET  |  | PART NO.                  | FX16-31P-0. 5SDL               |   |
|  | HIROSE ELECTRIC CO., LTD.  |  | CODE NO.                  | CL575-3322-7-00                |  1/1 |