

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ⁽¹⁾	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽²⁾	
	VOLTAGE	100 V AC	STORAGE HUMIDITY RANGE	40 % TO 70 % ⁽²⁾	
	CURRENT	0.5 A (SIGNAL CONTACT) ⁽³⁾ 3 A (MF CONTACT)	OPERATING HUMIDITY RANGE	RELATIVE HUMIDITY 85% max (NOT DEWED)	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING		CONFIRMED VISUALLY.		x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		100 mA(DC OR 1000Hz)	SIGNAL CONTACT : 90 mΩ MAX. MF CONTACT : 30 mΩ MAX.	x	—
INSULATION RESISTANCE		250 V DC.	1000 MΩ MIN.	x	—
VOLTAGE PROOF		300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	—
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE: 70 N MAX. WITHDRAWAL FORCE: 7 N MIN.	x	—
MECHANICAL OPERATION		500 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL CONTACT : 100 mΩ MAX. MF CONTACT : 40 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
VIBRATION		FREQUENCY 10 TO 55 TO 10Hz, APPROX 5min SINGLE AMPLITUDE : 0.75 mm, 10 CYCLES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
SHOCK		490 m/s ² , DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.		x	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.	① CONTACT RESISTANCE: SIGNAL CONTACT : 100 mΩ MAX. MF CONTACT : 40 mΩ MAX.	x	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85 °C TIME 30 → 30 min. UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN 2~3 MIN)	② INSULATION RESISTANCE : 1000 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
SULFUR DIOXIDE		EXPOSED AT 25±2°C, 75±5%RH, 25 PPM FOR 96 h. (TEST STANDARD: JIS C 60068)	NO HEAVY CORROSION.	x	—
RESISTANCE TO SOLDERING HEAT		1)REFLOW SOLDERING : PEAK TMP : 260°C MAX REFLOW TMP: 220°C MIN FOR 60sec 2) SOLDERING IRONS : 360°C MAX. FOR 5 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.	x	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE 240±3°C FOR IMMERSION DURATION, 3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARKS ⁽¹⁾ INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. ⁽²⁾ *STORAGE* MEANS A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE ASSEMBLY TO PCB. ⁽³⁾ THE RATED CURRENT APPLIES TO PER CONTACT. APPLY 0.4A WHEN ALL THE CONTACTS ARE USED FOR CURRENT CARRYING. Unless otherwise specified, refer to JIS-C-5402.			APPROVED	HS. OKAWA	14. 07. 16
			CHECKED	HT. YAMAGUCHI	14. 07. 15
			DESIGNED	TH. SANO	14. 07. 15
			DRAWN	TH. SANO	14. 07. 15
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-349391-00
HRS	SPECIFICATION SHEET		PART NO.	FX18-120S-0. 8SV10	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL579-0059-2-00	△ 1/1