APPLICA	BLE STAN	DARD									
		RATING TURE RANGE	−25°C TO +85°C	+85°C STORAG		GE ATURE RANGE			−25°C TO +60°C		
	OPERATING & STORAGE HUMIDTY RANGE		85%MAX						TINNED ANNEALED CO		₹
RATING	VOLTAGE		AC 125V		APPLIC	ABLE C	CABLE	SIZE : AWG28 STRANDING : 7/0.12			
	CURRENT		0.5 A	0.5 A				NSULATION DIAMETER : ϕ		φ0.9:	±0.04
			SPECI	IFIC,	ATIO	NS_					
	EM	TEST METHOD				REQUIREMENTS				QT	AT
CONSTR		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.					T v
GENERAL EXAMINATION MARKING		CONFIRMED VISUALLY.				ACCORDING TO DRAWING.				X	
	ICAL CHAI	RACTERIS								^	
CONTACT RE		100 mA (DC OR 1000 Hz).				50 mΩ MAX. (SIGNAL) 1				X	X
INSULATION	RESISTANCE	100 V DC.				1000 ΜΩ ΜΙΝ.				X	
VOLTAGE PF	ROOF	250 V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN.				X	+
MECHAN	IICAL CHA	RACTERIS	STICS								
INSERTION A		MEASURED BY APPLICABLE CONNECTOR.			INSERTION FORCE 43 N MAX. WITHDRAWAL FORCE 3.8 N MIN.				Х	_	
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.				1) CONTACT RESISTANCE 70 mΩ MAX. 1 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				> x	_
VIBRATION		FREQUENCY 10 TO 55 Hz SINGLE AMPLITUDE 0.75 mm, 5 min/CYCLE, TOTAL 10 CYCLES.				1) NO ELECTRICAL DISCONTINUITY OF 10 µs. 2) NO DAMAGE, CRACK AND LOOSENESS				X	-
SHOCK		$490~\text{m/s}^2$ DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				OF PARTS.				X	_
ENVIRON	MENTAL	CHARACT									
THERMAL SHOCK		TEMP $-55 \rightarrow +5$ TO $+35 \rightarrow +85 \rightarrow +5$ TO $+35 \circ C$ TIME $30 \rightarrow 5 \rightarrow 30 \rightarrow 5$ min. UNDER 5 CYCLES.			1) CONTACT RESISTANCE: 70 mΩ MAX. 1 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				\times	-	
HUMIDITY LIFE		TEMPERATURE 40 °C, HUMIDITY 90 TO 95 %, FOR 96 h			1) INSULATION RESISTANCE: 100 MΩ MIN. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.				X	_	
CORROSION SALT MIST		EXPOSED AT 5 % SALT WATER, FOR 48 h.			NO HEAVY CORROSION THAT LOSE FUNCTION.				1. X	-	
COUNT DESCRIPTION		SCRIPTION O	DF REVISIONS DESIG			NED T			CHECKED		<u> </u>
1 1 1		DIS-E-003445			TF. HIGASHIYAMA		1		KN. ICHIKAWA		09. 29
REMARK	1	NDUCTOR RESISTANCE OF CABLE.				APPR		<u> </u>			10. 07
I ^—					CHECK		KED			10. 07	
1—		IS HELD WITH "DH-51-CV * B", "DH30B-51S" AND "DH-51-CT * B", "DH30B-51S" AND "DH60A-51P".				DESIGN			MO. SHIMOYAMA		
Unless otherwise specified, refe						DRAV			TM. ONO		10. 07
Note QT:Qualification Test AT:Assurance						RAWING NO.			ELC4-126597-00		
LDC	SF	PECIFICA	TION SHEET		PART NO.			DH30B-51S			
H \(\mathbf{K}\)			TRIC CO., LTD.		CODE NO.		CI	CL244-0020-9-00			1/1