

APPLICABLE STANDARD		UL approved. (E52653)			
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	AC 125 V , DC 125 V		WIRE SIZE	MAX AWG#16
	CURRENT	10 A		APPLICABLE CABLE	φ 7.3±0.2
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X X
MARKING		CONFIRMED VISUALLY.			X X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A		5 mΩ MAX.	X X
INSULATION RESISTANCE		500 V DC.		1000 MΩ MIN.	X X
VOLTAGE PROOF		1250 V AC. FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X X
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND WITHDRAWAL FORCES		BY STEEL GAUGE.		INSERTION AND WITHDRAWAL FORCES : — N MIN.	— —
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.		INSERTION AND WITHDRAWAL FORCES LOCKING DEVICE WITH UNLOCK : 30 N MAX. LOCKING DEVICE WITH LOCK : — N MAX.	X —
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.		CONTACT RESISTANCE: 10 mΩ MAX.	X —
VIBRATION		FREQUENCY: 10 → 55 → 10 (Hz) (1CYC,5min), SINGLE AMPLITUDE 0.75 mm, AT 10 CYC, FOR 3 DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X —
SHOCK		IN OPPOSITE DIRECTIONS OF EACH 3 DEMENSION AXIS FOR 3 TIMES AT 490 m/s ² DURATIONS OF PULSE 11 ms.		① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X —
BREAKING STRENGTH		MAX 100 N SHALL BE APPLIED TO CABLE IN UP AND DOWN, LEFT AND RIGHT DIRECTIONS WHEN MATED.		NO BREAKAGE MAX 100N.	X —
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.		① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→ R/T ⁽¹⁾ → +85 → R/T °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.		① INSULATION RESISTANCE: 100 MΩ MIN. . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		NO HEAVY CORROSION RUINS THE FUNCTION.	X —
DRY HEAT		EXPOSED AT + 85 °C, 96 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
COLD		EXPOSED AT - 55 °C, 96 h.		NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X —
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, +350±10°C, FOR IMMERSION DURATION, 5±1 s.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X —
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, +350±10°C FOR IMMERSION DURATION, 2 TO 3 s.		SOLDER SURFACE TO BE FREE FROM PIN-HOLE, NO WETTING AND OTHER DEFECTS.	X —
SEALING ⁽²⁾		EXPOSED AT A DEPTH OF 1.8 m FOR 48 h.		NO WATER PENETRATION INSIDE CONNECTOR.	X —
AIR TIGHTNESS ⁽²⁾		APPLY AIR PRESSURE 17.6kPa FOR 0.5min TO INSIDE CONNECTOR.		NO AIR BUBBLES INSIDE CONNECTOR.	X —
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0					
REMARK				APPROVED	HY. KOBAYASHI 18.02.22
NOTES(1) R/T : ROOM TEMPERATURE				CHECKED	HY. KOBAYASHI 18.02.22
(2) SEALING AND AIRTIGHTNESS SHALL BE TESTED BY APPLICABLE CONNECTOR.				DESIGNED	TY. SUZUKI 18.02.21
Unless otherwise specified, refer to IEC 60512 (JIS C 5402).				DRAWN	HM. SAITO 18.02.19
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-117070-31-00
HRS	SPECIFICATION SHEET		PART NO.	LF10WBPD-4P (31)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL136-0017-1-31	△ 1/1