

APPLICABLE STANDARD							
RATING	OPERATING TEMPERATURE RANGE	- 55°C TO + 85°C (90%RH MAX)		STORAGE TEMPERATURE RANGE	- 55°C TO + 85°C (90%RH MAX)		
	POWER	—W		CHARACTERISTIC IMPEDANCE	50Ω (0 TO 6 GHz)		
	PECULIARITY	—		APPLICABLE CABLE	FWS5032 (KURABE INDUSTRIAL CO., LTD.) RF-MF50141 (NISSEI ELECTRIC CO., LTD.) J12B1481 (Junkosha Inc.)		
SPECIFICATIONS							
ITEM		TEST METHOD		REQUIREMENTS		QT	AT
CONSTRUCTION							
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X	X
MARKING		CONFIRMED VISUALLY.				—	—
ELECTRIC CHARACTERISTICS							
CONTACT RESISTANCE	100 mA MAX (DC OR 1000 Hz).	CENTER CONTACT		10 mΩ MAX.	X	X	
		OUTER CONTACT		5 mΩ MAX.	X	X	
INSULATION RESISTANCE	500 V DC.			500 MΩ MIN.	X	X	
VOLTAGE PROOF	500 V AC FOR 1 min. CURRENT LEAKAGE 2mA MAX.	NO FLASHOVER OR BREAKDOWN.			X	X	
VOLTAGE STANDING WAVE RATIO	FREQUENCY 0.045 TO 6 GHz	VSWR		1.2 MAX.	X	—	
INSERTION LOSS	FREQUENCY TO GHz			dB MAX.	—	—	
MECHANICAL CHARACTERISTICS							
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE.	INSERTION FORCE		N MAX.	—	—	
		EXTRACTION FORCE		N MIN.	—	—	
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION FORCE		15 N MAX.	X	—	
		EXTRACTION FORCE		6~15 N	X	X	
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.	1) CONTACT RESISTANCE: CENTER CONTACT 20 mΩ MAX. CHANGE OUTER CONTACT 10 mΩ MAX. CHANGE 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			X	—	
VIBRATION	FREQUENCY 10 TO 500 Hz SINGLE AMPLITUDE 0.75 mm, 98 m/s ² AT 12 CYCLES FOR 3 DIRECTIONS. (TOTAL 36 CYCLES)	1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			X	—	
SHOCK	735 m/s ² DIRECTIONS OF PULSE 6 ms AT 3 TIMES FOR 3 DIRECTIONS.				X	—	
CABLE CLAMP ROBUSTNESS (AGAINST CABLE PULL)	APPLYING A PULL FORCE THE CABLE AXIALLY AT 19.6 N MAX.	1) NO WITHDRAWAL AND BREAKAGE OF CABLE. 2) NO BREAKAGE OF CLAMP.			X	—	
ENVIRONMENTAL CHARACTERISTICS							
DAMP HEAT	EXPOSED AT 40 °C, 95 % (96 h)	1) INSULATION RESISTANCE: 10 MΩ MIN. (AT HIGH HUMIDITY) 2) INSULATION RESISTANCE: 500 MΩ MIN. (AT DRY) 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			X	—	
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → 20~35 → +85 → 20~35 °C TIME 30 → 3 → 30 → 3 min UNDER 5 CYCLES.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			X	—	
CORROSION SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 48h.	NO HEAVY CORROSION.			X	—	
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE		
△							
REMARK RoHS COMPLIANT			APPROVED	MH. YAMANE	10. 10. 27		
			CHECKED	TS. NOBE	10. 10. 27		
			DESIGNED	NK. OOSAWA	10. 10. 26		
			DRAWN	NK. OOSAWA	10. 10. 26		
Unless otherwise specified, refer to JIS C 5402.							
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-303198-40		
HRS	SPECIFICATION SHEET		PART NO.	MMCX-LP-088 (40)			
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL339-0020-1-40			
				△	1/1		