



APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)	
	VOLTAGE	30 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)	
	CURRENT	0.2 A	APPLICABLE CABLE	t=0.2±0.03mm, GOLD PLATING	
SPECIFICATIONS					
ITEM		TEST METHOD		REQUIREMENTS	QT AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×
MARKING		CONFIRMED VISUALLY.			×
ELECTRICAL CHARACTERISTICS					
VOLTAGE PROOF		90 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	×
INSULATION RESISTANCE		100 V DC.		50 MΩ MIN.	×
CONTACT RESISTANCE		AC 20 mV MAX (AC:1 KHz) , 1 mA .		100 mΩ MAX. INCLUDING FPC BULK RESISTANCE (L=12)	×
MECHANICAL CHARACTERISTICS					
VIBRATION		FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, FOR 10 CYCLES IN 3 AXIAL DIRECTIONS		① NO ELECTRICAL DISCONTINUITY OF 1 μs.	×
SHOCK		981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		② CONTACT RESISTANCE: 100 mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
MECHANICAL OPERATION		10 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
FPC RETENTION FORCE		MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.20mm AT INITIAL CONDITION.)		DIRECTION OF INSERTION : 0.15N × NUMBER OF CONTACTS MIN. (note 1)	×
ENVIRONMENTAL CHARACTERISTICS					
CORROSION SALT MIST		EXPOSED AT 35±2 °C , 5 % SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS. ③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	×
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55→+15TO+35→+85→+15TO+35°C TIME 30→ 2 TO 3 → 30→ 2 TO 3 min UNDER 5 CYCLES.		① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.			×
DAMP HEAT,CYCLIC		EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.		① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△					
REMARK			APPROVED	NF. MIYAZAKI	16. 03. 08
			CHECKED	YH. MICHIDA	16. 03. 08
			DESIGNED	KN. KOBAYASHI	16. 03. 08
Unless otherwise specified, refer to IEC 60512.			DRAWN	RN. IIDA	16. 03. 08
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-158578-99-00
HRS	SPECIFICATION SHEET		PART NO.	FH36W-**S-0. 3SHW (99)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL580	△ 1/2

SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
DRY HEAT	EXPOSED AT	85±2 °C, 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX.	x	—
COLD	EXPOSED AT	-55±3°C, 96 h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% 25±5 ppm FOR 96 h.		① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.		③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	x	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235 ±5°C FOR IMMERSION DURATION, 2±0.5 sec.		A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	x	—
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : PEAK TMP. 250 °C MAX . REFLOW TMP. OVER 230 °C WITHIN 60 sec. 2) SOLDERING IRONS : TMP. 350 ± 10 °C FOR 5±1 sec .		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS. (note 2)	x	—
<div>(note 1)</div> <div>THIS PRODUCT HAS FLIP-LOCK CONSTRUCTION. FASTEN FPC ON PCB OR SOMETHING FIXED IF FORCE IN VERTICAL DIRECTION SHALL BE PREDICTED.</div> <div>(note 2)</div> <div>BLISTERS WHICH MAY OCCUR IN HOUSING DO NOT AFFECT PRODUCT PERFORMANCE.</div>					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-158578-99-00	
	SPECIFICATION SHEET		PART NO.	FH36W-**S-0. 3SHW (99)	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL580	 2/2