

Features


- 1 Ultra Low profile 1.18mm height
- 2 Reverse card insertion protection
- 3 Buckling prevention eliminates contact damage
- 4 Card detection switch (Normally Close)
- 5 Easy inspection with exposed contact design




The world's lowest profile in its Class 1.18 mm*

* As push-push type micro SIM card connector as of Feb.2020

Dimensions



Buckling prevention design



Specifications

Rated Current	0.5A
Rated Voltage	10V AC
Operating Temperature	-30°C to +85°C
Contact Resistance	100mΩ Max.
Withstanding Voltage	500V AC for 1 minute
Insulation Resistance	1,000MΩ Min. (500V DC)
Mating Durability	5,000 times

• RoHS compliant, Halogen-free product*

*This product satisfies halogen free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1,500ppm maximum total of chlorine and bromine.

※ Please contact Hirose's sales representative prior to adopting the products to in-vehicle devices.