


Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 TABLE 1 SHOWS APPLICABLE CRIMP CONTACT AND APPLICABLE TOOL.
  - 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ②: 3 TO 4 N·m  
LOCTITE 242 HENKEL JAPAN OR EQUIVALENT IS  
RECOMMENDED TO PREVENT REF. NO. ② FROM LOOSENING.
  - 3 MAKE SURE THAT REF. NO. ② DOES NOT HAVE ANY FACTORS TO  
REDUCE WATER-RESISTANCY, SUCH AS SCRATCH, TWIST,  
PINCHING, OR DUST.

1 TABLE 1

		LOOSE PIECE CONTACT	STRIP CONTACT
APPLICABLE CRIMP CONTACT		HR22-SC-122 (CL122-0016-6)	HR22-SC-222 (CL122-0008-8)
APPLICABLE CABLE	SIZE	AWG#24~28	
	JACKET DIAMETER	Φ0.7~Φ1.15	
APPLICABLE CRIMPING TOOL		HR22-TA2428HC	AUTOMATIC CRIMPING MACHINE:CM-105 APPLICATOR:AP105-HR22-2
CONTACT EXTRACTION TOOL		RP6-SC-TP	

3	SILICONE RUBBER	(BLACK)			
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	5	BRASS	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	4	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT △	DESCRIPTION OF REVISIONS	
<b>HRS</b> HIROSE ELECTRIC CO., LTD.		APPROVED : SU. OBARA	11.02.18	DRAWING NO. EDC3-045137-73	
		CHECKED : HY. KISHI	11.02.18	PART NO. HR22-12WTRA-20SC(73)	
		DESIGNED : WR. AJIRO	11.02.18	CODE NO. CL122-0021-6-73	
		DRAWN : WR. AJIRO	11.02.18		
		DESIGNED	CHECKED	DATE	