


Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- ① THREAD PORTION OF REF. NO.① IS APPLIED WITH PRECOATING TO PREVENT LOOSENESS.
HOWEVER THE ADHESIVE EFFECTIVENESS IS DECREASED WHEN REUSED.
△ THEREFORE, TREAD PORTION APPLIES TO COAT WITH LOCTITE 263 MANUFACTURED BY HENKEL JAPAN OR EQUIVALENT.
 - ② THE RECOMMENDED TIGHTENING TORQUE OF REF. NO.⑤ TO BE 1 N·m.
 - ③ THE TIP OF REF. NO.⑩ SHALL BE FIXED TO THE CONCAVE PORTION WITH REF. NO.⑪ CLAMPED TO THE CABLE.
OPPOSITE SIDE DIMENSION OF A HEXAGON SOCKET OF REF. NO.⑩ IS 1.27mm.
AND THE RECOMMENDED TIGHTENING TORQUE OF REF. NO.⑩ TO BE 0.3 TO 0.4 N·m.
 - ④ MANUAL CRIMPING TOOL OF REF. NO.⑪ : HR10A-TC- 02
(THE HOLE DIAMETER FOR CRIMPING : Ø5.3)
 - 5 ROTATION EXAMPLES OF REF. NO.① AND ⑧ ARE SHOWN.
 - ⑥ OVER PLATING : GOLD 0.2µm min.
UNDER PLATING : NICKEL 2µm min.
 - △ 7 THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0361-00.

NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
6	BRASS	NICKEL PLATING			
5	BRASS	NICKEL PLATING	11	BRASS	
4	EPDM	(BLACK)	10	STEEL	NICKEL PLATING JIS B 1177 HEXAGON SOCKET SCREW M2.6X0.45X3
3	PHOSPHOR BRONZE	⑥	9	EPDM	(BLACK)
2	PPS	(BLACK) 94V-0	8	EPDM	(BLACK)
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	7	PHOSPHOR BRONZE	NICKEL PLATING

UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	2	DIS-C-00016975	HT. ZENBA	EJ. KUNII	20240229

APPROVED : TM. AKIYAMA	20051201	DRAWING NO.	EDC3-048670-72
CHECKED : TM. AKIYAMA	20051201	PART NO.	HR25-7TP-4P(72)
DESIGNED : HS. KAWASHIMA	20051119	CODE NO.	CL0125-0001-8-72
DRAWN : HS. KAWASHIMA	20051119		