

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICATION STANDARD											
RATING	OPERATING TEMPERATURE RANGE		-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE		-10 °C TO 60 °C			
	VOLTAGE		AC 50 V			OPERATING HUMIDITY RANGE		RELATIVE HUMIDITY : 95 % MAX (NO DEW CONDENSATION IS PERMITTED)			
	CURRENT		0.3 A								
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENT				QT/AT	
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING				X X	
MARKING		CONFIRMED VISUALLY.								X X	
ELECTRICAL CHARACTERISTICS											
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz).				70 mΩ MAX.				X X	
INSULATION RESISTANCE		100 V DC.				100 MΩ MIN.				X -	
VOLTAGE PROOF		150 V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN				X X	
MECHANICAL CHARACTERISTICS											
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.				INSERTION FORCE: 60 N MAX. WITHDRAWAL FORCE: 2.5 N MIN				X -	
MECHANICAL OPERATION		50 TIMES INSERTION AND EXTRACTIONS.				1)CONTACT RESISTANCE: 80 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PART.				X -	
VIBRATION		FREQUENCY: 10 TO 55 Hz. SINGLE AMPLITUDE: 0.75 mm, - m/s ² AT 10 CYCLES FOR 3 DIRECTIONS.				1)NO ELECTRICAL DISCONTINUITY OF 1 μs MIN. 2)NO DAMAGE, CRACK AND LOOSENESS OF PART.				X -	
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.								X -	
ENVIRONMENTAL CHARACTERISTICS											
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2 °C, 90~95 %, 96 h.				1)CONTACT RESISTANCE: 80 mΩ MAX. 2)INSULATION RESISTANCE: 100 MΩ MIN.				X -	
RAPID CHAGE OF TEMPERTURE		TEMPERTURE -55→15~35→ 85→15~35°C TIME 30→ 2~ 3→ 30→ 2~ 3min. UNDER 5 CYCLES.				3)NO DAMAGE, CRACK AND LOOSENESS OF PART.				X -	
DRY HEAT		EXPOSED AT 85 °C, 96 h.				1)CONTACT RESISTANCE: 80 mΩ MAX.				X -	
COLD		EXPOSED AT -55 °C, 96 h.				2)NO DAMAGE, CRACK AND LOOSENESS OF PART.				X -	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.				NO HEAVY CORROSION.				X -	
SULPHUR DIOXIDE		EXPOSED IN 10 PPM FOR 96 h. (TEST STANDARD:JIS C 0090)				1)CONTACT RESISTANCE: 80 mΩ MAX. 2)NO HEAVY CORROSION.				X -	
RESISTANCE TO SOLDERING HEAT		REFLOW RECOMMENDED TEMPERATURE PROFILE 25°C (60 S) 150°C 160°C 240°C 5 S MAX 200°C (30 S) (20~30 S) TO BE TESTED UNDER THE ABOVE CONDITIONS.				NO MELTING OF RESIN WHICH AFFECTS THE PERFORMANCE OF COMPONENT				X -	
SOLDRABILITY		SOLDERED AT SOLDER TEMPERATURE, 235 °C FOR IMMERSION DURATION, 2 s.				NO PINHOLE OR DEWETTING ON SOLDERED SURFACE.				X -	
REMARKS						DRAWN		DESIGNED		CHECKED	
UNLESS OTERWISE SPECIFIED ,REFER TO JIS C 5402.						00.01.15		00.01.15		00.01.17	
NOTE						QT: QUALIFICATION TEST		AT: ASSURANCE TEST		X: APPLICABLE TEST	
						SPECIFICATION SHEET		PART NO.			
HIROSE ELECTRIC CO.,LTD.								FX11B - 100P - SV (22)			
CODE NO. (OLD)		DRAWING NO		CODE NO						1	
CL		ELC4 - 152610 - 02		CL 573 - 0553 - 0 - 22						1	