



Fig.2(1:1)



A-A



- NOTES
- PLATING(REF.NO. ③、④、⑤)
CONTACT AREA : GOLD 0.2μm min
OTHERS : GOLD AND NICKEL
UNDER PLATING : NICKEL 2μm min
 - THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑦ TO BE 1.5 TO 2N·m.
THREAD LOCKER TO THE THREADED PORTION OF REF.NO. ① IS RECOMMENDED TO PREVENT REF.NO. ⑦ FROM LOOSING.
RECOMMENDED THREAD LOCKER:LOCTITE 271, HENKEL JAPAN LTD.
 - THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑫ TO BE 1 TO 1.5N·m.
THREAD LOCKER AND LOCK PRIMER TO THE THREADED PORTION M14.5×0.75 OF REF.NO. ⑦ IS RECOMMENDED TO PREVENT REF.NO. ⑫ FROM LOOSING.
RECOMMENDED THREAD LOCKER AND LOCK PRIMER : LOCTITE 271, LOCK PRIMER 7649, HENKEL JAPAN LTD.
 - FASTEN REF.NO. ⑬ TO THE CABLE WITH THE CABLE CRIMPING TOOL.
AND MAKE REF.NO. ⑬ CONTACT WITH REF.NO. ⑨(REFER TO Fig.1).
REFER TO THE TECHNICAL SPECIFICATION ATAD-C0099 FOR DETAILS.
APPLICABLE CABLE CRIMPING TOOL : LF-TC-01 (CL150-0234-6)
 - APPLICABLE CABLE ASSEMBLY FIXTURE : LF13BJ-T01 (CL150-0238-7)
CABLE ASSEMBLY FIXTURE IS USED AS A RECEPTACLE STAND OF EXTRACT AND THE PART NUMBER ① OF AN ASSEMBLY.
 - Fig.2 SHOWS THE APPEARANCE AFTER ASSEMBLY.
 - ROTATION EXAMPLES OF REF. NOS. ⑦ AND ⑫ TO ① ARE SHOWN.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE

7	ZINC ALLOY	NICKEL PLATING			
6	PHOSPHOR BRONZE	NICKEL PLATING	13	BRASS	NICKEL PLATING
5	PHOSPHOR BRONZE	①	12	PPS	(NATURAL, BROWN) UL94V-0
4	PHOSPHOR BRONZE	①	11	POLYAMIDE	(NATURAL, MILKY WHITE) UL94V-0
3	COPPER ALLOY	①	10	CHLOROPRENE RUBBER	(BLACK)
2	PPS	(BLACK) UL94V-0	9	PHOSPHOR BRONZE	NICKEL PLATING
1	ZINC ALLOY	NICKEL PLATING	8	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD) CL	DRAWN kabe 05.5.12	DESIGNED H. Zemba 05.05.13	CHECKED M. Sato 05.5.13	APPROVED M. Yoshida 05.05.16	RELEASED
SCALE 4 : 1 UNITS mm	DRAWING NO. EDC3-114405	PART NO. LF13WBJ-11S	CODE NO. CL136-2012-9	1/1	
	HIROSE ELECTRIC CO., LTD				