






Feb. 1. 2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD						
 RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ^{(1) (2)}	STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽³⁾		
	VOLTAGE	60 V AC ⁽⁵⁾	OPERATING HUMIDITY RANGE	RH 85 % MAX ^{(2) (4)}		
	CURRENT	0.5 A ⁽⁵⁾	STORAGE HUMIDITY RANGE	RH 70 % MAX ^{(3) (4)}		
	APPLICABLE CABLE	AWG 36, 40 THIN COAXIAL CABLE				
SPECIFICATIONS						
ITEM	TEST METHOD		REQUIREMENTS	QT	AT	
CONSTRUCTION						
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x	x	
MARKING	CONFIRMED VISUALLY.			x	x	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
	2	DIS-F-004353	KN. SHIBUYA	HT. YAMAGUCHI	09. 12. 15	
	REMARKS			APPROVED	HS. OKAWA	08. 05. 24
	(1) INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. (2) OPERATING TEMPERATURE SHOULD BE -55 TO 40°C WHEN HUMIDITY EXCEEDS 80% RH. (3) THE SPECIFICATION IS APPLIED TO THE PRE-ASSEMBLED COMPONENT AND THE CABLE ASSEMBLED PRODUCT BOTH IN DELIVERY AND STORAGE, BEFORE ASSEMBLED TO PCB. (4) THERE MUST NOT BE DEWFALL. (5) IT IS THE MAXIMUM VALUE OF CONNECTOR. CONFIRM THE SPECIFICATION OF THE CABLE.			CHECKED	HT. YAMAGUCHI	08. 05. 24
	Unless otherwise specified, refer to JIS-C-5402.			DESIGNED	TS. SHIBUYA	08. 05. 24
				DRAWN	TS. SHIBUYA	08. 05. 24
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-158279-00		
	SPECIFICATION SHEET		PART NO.	FX16-21P-GNDL		
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL575-3331-8-00	 1/1	