




PANEL CUT OUT(REFERENCE)
PANEL THICKNESS:0.7~2.2mm

Part No.	Cable color
~066N1~	GRAY
~066N2~	BLACK
~066N3~	WHITE

- NOTE 1 Do not apply any excessive stress to the cable assembly position.
- 2 We indicate the length of the harness on the last of product name, 'L' part.

Tolerance for [L]

Length L [mm]	Tolerance [mm]
$50 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$


3. Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional.

- 4 Lock nut, tooth washer and o-ring are attached separately in other package.


5. Specifications are subject to change without notice.

- [PRECAUTIONS FOR HANDLING]

- ◆ Connector insertion and extraction
 - a. Connector shall be extracted vertically by specialised extraction JIG.
Part No.:U.FL-LP-N-2CCL Code:CL331-0494-5>
Never hold the cable when extracting the cable because it damages the connector.
 - b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.
- ◆ Allowable loads on the cable after the connectors are mated.
The figures below show the maximum allowable loads on the cable. Do not apply loads exceeding these values to the cable.



DIMENSIONS OF CONNECTOR



2	U. FL-LP-066HF	CL331-0558-6-00							
1	HRM-200-066WBPJBN	CL323-0946-0-00		3	RF-MF5013	NISSEI ELECTRIC CO., LTD.			
No.	PART NO.	CODE NO.		No.	PART NO.	MANUFACTURER			
UNITS mm		SCALE FREE		COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.		APPROVED	: TO. KATAYAMA	20200928	DRAWING NO.				
		CHECKED	: TO. KATAYAMA	20200928	PART NO. HWBPJ-UFLHF6-066N*-A-L				
		DESIGNED	: MK. INOUE	20200928	CODE NO.				
		DRAWN	: MK. INOUE	20200928					