


Apr.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Rev.	Count	Description of rev.	BY	CHKD	Date	Rev.	Count	Description of rev.	BY	CHKD	Date
Applicable standard		Universal Serial Bus Type-C Cable and Connector Specification Release 2.1 Universal Serial Bus Type-C Connectors and Cable Assemblies Compliance Document Revision 2.1b									
Rating	Voltage	48V AC/DC									
	Current	1.5A max. for each power pin (i.e., A1, A4, A9, A12, B1, B4, B9, B12) 1.25A max. for Vcon pin (i.e., B5) 0.25A max. for the others.									
Operating condition		-40℃~+105℃(Including temp. rise), 95% RH max.(Non-condensing)									
Storage condition		-10℃~+60℃(With packing), 15%~70% RH									

SPECIFICATIONS

No	TEST ITEM	TEST METHOD	TEST REQUIREMENT	QT	AT
CONSTRUCTION					
1	General Examination	EIA 364-18 Visual inspection	No physical damage	O	O
ELECTRICAL CHARACTERISTICS					
2	Low level contact resistance	EIA 364-23 Measure at 20mV max open circuit at 100mA max. (DC or 1000Hz) 4-wire measurement is required and the resistance of PCB termination shall be deducted from the reading.	Initial : 40mΩ max After test : 50mΩ max	O	-
3	Dielectric Withstanding Voltage	EIA 364-20 Measure per Method B with unmated condition. 100V AC RMS for 1 minute at sea level.	No disruptive discharge.	O	-
4	Insulation resistance	EIA 364-21 500V DC with unmated and mated condition.	100MΩ min.	O	-
MECHANICAL CHARACTERISTICS					
5	Insertion force	EIA 364-13 Measure at 12.5mm/minute min.	Initial : 5N ~ 20N After test : 5N ~ 20N (with virgin plug)	O	-
6	Extraction force	EIA 364-13 Measure at 12.5mm/minute min.	Initial : 8N ~ 20N After test : 6N ~ 20N (with virgin plug)	O	-
7	Durability	EIA 364-09 Mated 10,000 times Mechanically operated : 500cycles/hr Mating stroke : 2.75mm Insertion, extraction force shall be measured at a maximum speed of 12.5mm/min	No physical damage.	O	-
8	Random Vibration	EIA 364-28	No physical damage.	O	-


Remarks	Drawn	Designed	Checked	Approved	Release
	YJ.KIM 22.06.28	YJ.KIM 22.06.28	H.J.LEE 22.06.28	H.J.LEE 22.06.28	

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable

Drawing No. ELC4-632813	CL No. CL 6240-0029-8	Part No. CX70M1-24P
-----------------------------------	---------------------------------	-------------------------------

		Test Condition VII, Test Letter D Mated specimens to 3.10 G's RMS between 20 to 500Hz 15 minutes in each of 3 mutually perpendicular planes.	No discontinuity of 1μs of longer duration when mated connector during test.		
ENVIRONMENTAL CHARACTERISTICS					
9	Temperature Rise	EIA-364-70, method B : A current of 6.0 A shall be applied collectively to VBUS pins (i.e., pins A4, A9, B4, and B9) and 1.25 A applied to the Vconn pin (i.e., B5 of the plug connector) with the return path through the corresponding GND pins (i.e., pins A1, A12, B1, and B12). A minimum current of 0.25 A shall also be applied individually to all the other contacts.	Temperature rise shall not exceed 30°C	O	-
10	Temperature Life	EIA 364-17, Method A 105°C without applied voltage for 120 hours.	No physical damage.	O	-
11	Cyclic Temperature and Humidity	EIA 364-31 25°C~65°C, 80~100% RH, 24hours a cycle, repeat 10 cycles	No physical damage.	O	-
12	Thermal Shock	EIA 364-32, Test Condition I 10 cycles -55°C and +105°C	No physical damage.	O	-
13	Solderability	EIA 364-52 Dwell in 245±5°C of the solder bath for 5 sec.	Solder coverage shall be 95% min. of the immersed surfaces.	O	-
14	Salt Spray	EIA 364-26 5% of NaCl in 35°C for 48 hours.	No corrossions that affect to the connector operation.	O	-
15	Reflow test	Reflow profile [Fig.1] Peak 250°C max for 10 sec 2 times.	Co-planarity Before&after Reflow 0.10max No deformation of mold No shape of blister and popcorn	O	-

REMARKS



[Fig.1] REFLOW TEMPERATURE

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable					
Drawing No. ELC4-632813		CL No. CL 6240-0029-8		Part No. CX70M1-24P	
HRS HIROSE KOERA.CO.,LTD			PRODUCT SPECIFICATION		2/5

Test Sequence Table

No	Test item	Test Group									
		A	B	C	D	E	F	G	H	I	J
1	Examination of product	1, 5	1, 13	1, 5	1, 5	1, 5	1, 3	1, 5	1, 3	1, 3	1, 5
2	Low Level Contact Resistance	2, 4	2, 12	2, 4	2, 4	2, 4		2, 4			2, 4
3	Dielectric Withstanding Voltage		3, 11								
4	Insulation Resistance		4, 10								
5	Insertion force		5, 9								
6	Extraction force		6, 8								
7	Durability		7								
8	Random Vibration	3									3
9	Temperature Rise									2	
10	Temperature Life			3							
11	Cyclic Temperature and Humidity				3						
12	Thermal Shock					3					
13	Solderability						2				
14	Salt Spray							3			
15	Reflow Test								2		

REMARKS

1) Numbers in the table above indicate the sequence corresponding to each test group.

[Note] QT : Qualification test, AT : Assurance test, O : Applicable, - : Not applicable		
Drawing No. ELC4-632813	CL No. CL 6240-0029-8	Part No. CX70M1-24P
HRS HIROSE KOERA.CO.,LTD		PRODUCT SPECIFICATION
		3/5