







Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



ENGAGEMENT FIGURE (30:1)



SIGNAL CONTACT

BK11C0.6-10DP6-0.35V(800)



BK11C0.6-10DS6-0.35V(***)

POWER CONTACT



- NOTE
1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 2. CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μ m MIN
SMT LEAD : GOLD 0.05 μ m MIN
UNDERPLATING : NICKEL 1 μ m MIN
(SURFACE : SEALING)
 3. CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.
 4. A PART OF THE WALL COULD BE NOTCHED.
 5. DENT EXISTS IN THE INDICATED AREA FOR MANUFACTURING CONVENIENCE.

	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△	1	RE-6-1442	PJS	JHW		20. 03. 10	△						
△	4	RE-6-1988	PJS	JHW		20. 09. 02	△						
△							△						

4	PS	CLEAR (EMBOSSED CARRIER TAPE)											
3	COPPER ALLOY	2					7	PS	CLEAR (REINFORCEMENT COLLAR)				
2	COPPER ALLOY	2					6	PS	BLACK (PLASTIC REEL)				
1	LCP	UL94 V-0, BLACK					5	POLYESTER	CLEAR (COVER TAPE)				
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL
REMARKS								DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
								J. S. PARK	J. S. PARK	H. W. JO	H. W. JO	20. 03. 10	
								19. 10. 16	19. 10. 16	19. 10. 16	19. 10. 16		
CODE NO. (OLD)								DRAWING NO.		PART NO.		CODE NO	
								EDC3-632961-80		BK11C0.6-10DP6-0.35V(800)		CL 6664-0007-8-800	
								SCALE		HRS HIROSE KOREA CO., LTD.		1	
								10:1				3	
								UNITS					
								mm					

