

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	OPERATING TEMPERATURE RANGE		-55℃ ~ +85℃			STORAGE TEMPERATURE RANGE		-10℃ ~ +50℃(Packed Condition)			
	VOLTAGE		30V [AC(rms) / DC]			OPERATING OR STORAGE HUMIDITY RANGE		Relative Humidity 90% MAX(NOT DEWED)			
	CURRENT		0.4A [AC(rms) / DC]			APPLICABLE CABLE		FPC (t=0.2±0.03mm)			
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS			QT	AT	
CONSTRUCTION											
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT				ACCORDING TO DRAWING			O	O	
MARKING		CONFIRMED VISUALLY							O	O	
ELECTRICAL CHARACTERISTICS											
CONTACT RESISTANCE		MATE APPLICABLE FPC/FFC AND APPLY A CURRENT OF 1mA DC(OR 1,000Hz)				100mΩ MAX. INCLUDING FPC/FFC BULK RESISTANCE(L=8mm)			O	O	
INSULATION RESISTANCE		MATE APPLICABLE FPC/FFC AND APPLY A VOLTAGE OF DC 100V				500MΩ MIN.			O	O	
VOLTAGE PROOF		MATE APPLICABLE FPC/FFC AND APPLY A VOLTAGE OF AC 150V FOR 1 min.				NO FLASHOVER OR BREAKDOWN.			O	O	
MECHANICAL CHARACTERISTICS											
FPC RETENSION FORCE		MEASURE BY APPLICABLE FPC/FFC(t=0.2) AT INITIAL CONDITION				①HORIZONTAL DIRECTION : 0.25N X n MIN. ②VERTICAL DIRECTION : 0.25N X n MIN. (n : NUMBER OF CONTACTS)			O	-	
MECHANICAL OPERATION		20 TIMES INSERTIONS AND EXTRATIONS				①CONTACT RESISTANCE : 100mΩ MAX ②NO DAMAGE,CRACK AND LOOSENESS OF PARTS			O	-	
VIBRATION		FREQUENCY 10 ~ 55 Hz, TOTAL AMPLITUDE 1.5 mm AT 2h, IN 3 DIRECTIONS				①NO ELECTRICAL DISCONTINUITY OF 1μs. ②CONTACT RESISTANCE : 100mΩ MAX			O	-	
SHOCK		981m/s ² DIRECTION OF PULSE 6ms AT 3 TIMES IN 3 DIRECTIONS.				③NO DAMAGE,CRACK AND LOOSENESS OF PARTS			O	-	
ENVIRONMENTAL CHARACTERISTICS											
DAMP HEAT(STEADY STATE)		EXPOSED AT 40℃, 90~95 %, 96Hr.				①CONTACT RESISTANCE : 100mΩ MAX.			O	-	
RAPID CHAGE OF TEMPERATURE		TEMPERATURE : -55 → 15~35 → +85 → 15~35 ℃ TIME : 30 → 2~3 → 30 → 2~3 min. UNDER 5 CYCLES.				②INSULATION RESISTANCE : 100MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			O	-	
DAMP HEAT, CYCLE		TEMPERATURE -10→+65 HUMIDITY : 90~95% 10 CYCLE(240Hr)				①CONTACT RESISTANCE : 100mΩ MAX. ②INSULATION RESISTANCE : 100MΩ MIN. ③NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			O	-	
DRY HEAT		EXPOSED AT 85℃, 96Hr				①CONTACT RESISTANCE : 100mΩ MAX			O	-	
COLD		EXPOSED AT -55℃, 96Hr				②NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			O	-	
CORROSION SALT SPRAY		EXPOSED AT 35℃, 5 % SALT WATER SPRAY FOR 48Hr				①CONTACT RESISTANCE : 100mΩ MAX ②NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			O	-	
HYDROGEN SULPHIDE		EXPOSED IN 3 PPM FOR 96Hr. (TEST STANDARD : JEIDA-38)				③NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.			O	-	
RESISTANCE TO SOLDERING HEAT		REFLOW SOLDERING: PROFILE : 230℃ 60s, 250℃ MAX.				①NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS. ②NO DAMAGE OF ELECTRICAL PERFORMANCE			O	-	
SOLDER ABILITY		SOLDERED AT SOLDER TEMPERATURE, 245±3℃ FOR IMMERSION DURATION, 3±0.3 SEC				A NEW UNIFORM COATING OF SLODER SHALL COVER A MINIMUM OF 95% OF THE SURFACE BEING EMMERSED.			O	-	
REMARKS	CONDITIONS FOR TESTING				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED		
					M.H.LEE 17.09.29	M.H.LEE 17.09.29	CHO.D.H 17.09.29	SONG.H.C 17.09.29	ENG 17.09.29 DEPT		
UNLESS OTHERWISE SPECIFIED, REFER TO JIS C 5402.											
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET			PART NO. TF42-**S-0.35SH(800)					
CODE NO.(OLD)		DRAWING NO. SLC4-632416-80		CODE NO. CL ****_****_*		1 1					