

Features


- 1 **Ultra Low profile 1.18mm height**
- 2 **Incorrect card insertion prevention**
- 3 **Card fly-out prevention**
- 4 **Card detection switch**
- 5 **Easy inspection with exposed contact design**




The world's lowest profile in its Class
1.18 mm

*As push-push type micro SIM card connector as of Feb. 2017

Dimensions



Prevents card fly-out



⇒ **Holds nano SIM securely in place**

Specifications

Rated Current	0.5A
Rated Voltage	10V AC
Operating Temperature	-30 to +85°C
Contact Resistance	100mΩ Max.
Withstanding Voltage	500V AC for 1 minute
Insulation Resistance	1,000MΩ Min. (500V DC)
Mating cycles	5,000 times

- RoHS compliant, Halogen-free product*
- *This product satisfies halogen-free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1,500ppm maximum total of chlorine and bromine.
- ※ Please contact Hirose's sales representative prior to adopting the products to in-vehicle devices.