



	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△					
△						△					
APPLICABLE STANDARD											
RATING	Operating Temperature Range		-55℃ to 105℃ (Note1)			Storage Temperature Range		-10℃ to 60℃ (Note3)			
	Voltage		20% to 80% (Note2)			Storage Humidity Range		40% to 70% (Note3)			
	Applicable Connector		KW30-*P-*C(###)			Applicable Cable		AWG#28 to 30			
	Current		AWG 30 : 1.0A AWG 28 : 1.0A			Insulation Diameter		φ 0.64 mm			
SPECIFICATIONS											
ITEM		TEST METHOD				REQUIREMENTS			QT	AT	
CONSTRUCTION											
General Examination		Visually and by measuring instrument.				According to drawing.			O	O	
Marking		Confirmed visually.							O	O	
ELECTRICAL CHARACTERISTICS											
Contact Resistance		20mV MAX, 10mA (DC or 1000Hz).				20 mΩ MAX. (Note 4)			O	-	
Millivolt Level Method											
MECHANICAL CHARACTERISTICS											
Mechanical Operation		30 times insertion and extraction.				①Contact resistance : 20mΩ MAX. (Note 4) ②No damage, crack or looseness of parts.			O	-	
Crimp Tensile Strength		Pull out the cable after Crimp contact fixation.				AWG#28 : 16N MIN			O	-	
Vibration		Frequency 10 to 55 Hz, single amplitude 1.52 mm, at 2hours for 3 direction.				①No electrical discontinuity of 1 μ s. ②Contact resistance : 50 mΩ MAX. (Note 5)			O	-	
Shock		Acceleration 490 m/s ² duration of pulse 11 ms at 3times for 3 directions.				③No damage, crack or looseness of parts.			O	-	
ENVIRONMENTAL CHARACTERISTICS											
Damp Heat (Steady State)		Exposed at 40 ± 2 °C , humidity 90 to 95 %, 240 h.				①Contact resistance : 50 mΩ MAX. (Note 5) ②Insulation resistance : 100MΩ MIN. ③No damage, crack or looseness of parts.			O	-	
Rapid Change of Temperature		Temperature -55 °C → 105 °C Time 30min → 30min 25 Cycles. (The transferring time of the tank is 2 to 3 MIN) (After leaving the room temperature for 1 to 2h.)				①Contact resistance : 50 mΩ MAX. (Note 5) ②Insulation resistance : 100MΩ MIN. ③After Voltage proof test No flashover or breakdown. ④No damage, crack or looseness of parts.			O	-	
Note 1: Include the temperature rising by current. Note 2: No condensing Note 3: Apply to the condition of long term storage for unused products before PCB on board. After PCB on board, operating temperature and humidity range is applied for interim storage during transportation.											
Remark					DRAWN J.H.SHIN 22.05.20	DESIGNED J.H.SHIN 22.05.20	CHECKED S.M.LIM 22.05.20	APPROVED S.M.LIM 22.05.20	RELEASED		
Unless otherwise specified, refer to IEC 60512.											
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.			SPECIFICATION SHEET				PART NO. KW30A-2830PCFA (805)				
CODE NO.(OLD) CL		DRAWING NO. ELC4-633135			CODE NO. CL 6669-0045-9-805			1 2			

Dry Heat	Exposed at 105±2 °C, 250h	①Contact resistance : 50 mΩ MAX. (Note 5) ②Insulation resistance : 100MΩ MIN.	0	—
Cold	Exposed at -55±3 °C, 250h	③After Voltage proof test No flashover or breakdown. ④No damage, crack or looseness of parts.	0	—
Corrosion, Salt Mist	Exposed in 35±2 % salt water spray for 48h.	Contact resistance : 50 mΩ MAX. (Note 5)	0	—
Hydrogen Sulfide	Exposed in 40±2 °C, humidity 80±5% 3±1 ppm for 96h.	Contact resistance : 50 mΩ MAX. (Note 5)	0	—

(Note 4) The cable conductor resistance and crimping resistance and PCB circuit resistance is not considered.



(Note 5) The cable conductor resistance is not considered



NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST				
HIROSE KOREA CO.,LTD.		SPECIFICATION SHEET		PART NO. KW30A-2830PCFA (805)
CODE NO.(OLD) CL	DRAWING NO. ELC4-633135	CODE NO.	CL 6669-0045-9-805	2/2