




Mar.1.2025 Copyright 2025 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard					
Rating	Operating Temperature range	-40 °C to +105°C (Note1)	Storage Temperature range	-10 °C to +60°C (Note2)	
	Operating Humidity range	20% to 80%	Storage Humidity range	40% to 70% (Note2)	
	Applicable Connector	DF62WC-4EP-2.2C(##)	Voltage	AC/DC 250V	
	Applicable contact	DF62W-2226SC*	Current	AWG 22 : 3A	
	Applicable Insulation diameter	φ 0.98 to φ 1.2mm		AWG 24 : 2A AWG 26 to 30 : 1A	
Specifications					
Item	Test method	Requirements	QT	AT	
<b>Construction</b>					
General examination	Visually and by measuring instrument.	According to drawing.	X	X	
Marking	Confirmed visually.		X	X	
<b>Electric characteristics</b>					
Insulation resistance	500 V DC.	1000 MΩ MIN.	X	—	
Voltage proof	650 V AC for 1 min.	No flashover or breakdown.	X	—	
<b>Mechanical characteristics</b>					
Mechanical operation	30 times insertion and extraction.	No damage, crack or looseness of parts.	X	—	
Vibration	Frequency 10 to 55 Hz, single amplitude 0.75 mm, at 10 cycles for 3 direction.	No damage, crack or looseness of parts.	X	—	
Shock	490 m/s <sup>2</sup> duration of pulse 11 ms at 3 times each for 3 both axial directions.	No damage, crack or looseness of parts.	X	—	
<b>Environmental characteristics</b>					
Damp heat (Steady state)	Exposed at 40 ± 2°C , 90 to 95 %, 96 h. (After leaving the room temperature for 1~2h.)	①Insulation resistance: 1000 MΩ Min. ②No damage, crack or looseness of parts.	X	—	
Rapid change of temperature	Temperature -55°C→ +85°C Time 30min→ 30min Under 5 cycles. (The transferring time of the tank is 2~3 min) (After leaving the room temperature for 1~2h.)	①Insulation resistance: 1000 MΩ Min. ②No damage, crack or looseness of parts.	X	—	
<p>Note 1: Include the temperature rising by current.</p> <p>Note 2: Apply to the condition of long term storage for unused products before mount on pcb, After mounted on pcb, operating temperature and humidity range is applied for interim storage during transportation.</p>					
	Count	Description of revisions	Designed	Checked	Date
Remarks			Approved	HS. OKAWA	20190724
Unless otherwise specified, refer to IEC 60512.			Checked	SZ. ONO	20190724
			Designed	TO. KUROMATSU	20190724
			Drawn	TO. KUROMATSU	20190724
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test	Drawing No.	ELC-387673-00-00
	Specification sheet		Part No.	DF62WC-4S-2. 2C	
	HIROSE ELECTRIC CO., LTD.		Code No.	CL544-1051-0-00	 1/1