






RECOMMENDED LAND PATTERN DIMENSION OF PCB
(RECOMMENDED METAL MASK THICKNESS:0.15mm)




- NOTES
- 1 8 HATCHED PARTS:GROUND CIRCUIT.
 - 2 2 HATCHED PARTS:GROUND CIRCUIT.
 - 3 SMT LEAD-COPLANARITY:0.1 MAX.
 - 4 THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
 - 5 MAKE SURE WIDTH OF PATTERN IS WITHIN THAT OF LAND,OR LEAD MAY TOUCH PATTERN. (THIS APPLIES TO HATCHED AREA.)
 - 6 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

CROSS CUT SECTION - SIGNAL(5:1)



CROSS CUT SECTION - GROUND(5:1)



2	PHOSPHOR BRONZE	TIN-PLATING	3	PHOSPHOR BRONZE	CONTACT AREA:GOLD 0.1μm min.				
1	LCP	BEIGE UL94V-0			LEAD AREA :TIN-PLATING 1μm min.				
					UNDER PLATING : NICKEL 1μm min.				
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS			
UNITS mm			SCALE 4 : 1		DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : HS. OKAWA		08.06.26	DRAWING NO.		EDC3-151944-25		
		CHECED : HT. YAMAGUCHI		08.06.25	PART NO.		FX10A-80P/8-SV(71)		
		DESIGNED : SY. KAMIGA		08.06.23	CODE NO.		CL570-0001-5-71		
		DRAWN : HK. SUNADORI		08.06.17					
								1/1	