








RECOMMENDED LAND PATTERN DIMENSION OF PCB

3 FLOATING RANGE



DRAWING FOR MATING: REFERENCES (FREE)



6	POLYESTER	CLEAR
5	POLYSTYRENE	CLEAR
4	BRASS	TIN PLATING 1μm MIN
3	COPPER ALLOY	CONTACT: GOLD PLATING 0.1μm MIN LEAD : GOLD PLATING 0.03μm MIN UNDER : NICKEL PLATING 1μm MIN


2	POLYAMIDE	BLACK, UL94V-0
1	POLYAMIDE	BLACK, UL94V-0
NO.	MATERIAL	FINISH, REMARKS
UNITS	mm	SCALE 2:1
		COUNT
		DESCRIPTION OF REVISIONS
		DESIGNED
		CHECKED
		DATE
		APPROVED : HS. OKAWA 16.01.16
		CHECKED : HT. YAMAGUCHI 16.01.16
		DESIGNED : MT. ITANO 16.01.16
		DRAWN : MT. ITANO 16.01.16

DRAWING NO.	EDC-336319-20-00
PART NO.	FX20-40P-0.5SV15(20)
CODE NO.	CL570-1001-0-20




- NOTE
- 1 LEAD CO-PLANARITY IS 0.1mm MAX.
 - 2 THIS IS PACKAGED IN EMBOSSED CARRIER TAPE. (260 PCS/RL)
 - 3 FLOATING RANGE OF THIS CONNECTOR IS ±0.6mm MAX.
 - 4 BLEMISH AND HIT MARK CAN BE OCCURED THROUGH OUT THE MANUFACTURING PROCESS WHICH DOESN' T AFFECT QUALITY LEVEL.
 - 5 PLEASE NOTE THAT EXCESSIVE WRENCHING FORCE COULD DAMAGE THIS CONNECTOR.
PLEASE REFER TO THE GUIDELINE FOR DETAILED REGULATIONS OF THE MATING METHOD.

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

2 DRAWING FOR PACKING



REELING CONDITION FOR DELIVERY(FREE)



HRS	DRAWING NO.	EDC-336319-20-00
	PART NO.	FX20-40P-0.5SV15(20)
	CODE NO.	CL570-1001-0-20
		$\triangle$ 2/2