

APPLICABLE STANDARD						
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C ^{(1) (2)}		STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C ⁽³⁾	
	VOLTAGE	60 V AC ⁽⁵⁾		OPERATING HUMIDITY RANGE	RH 85 % MAX ^{(2) (4)}	
	CURRENT	0.5 A ⁽⁵⁾		STORAGE HUMIDITY RANGE	RH 70 % MAX ^{(3) (4)}	
	APPLICABLE CABLE	AWG 36, 40 THIN COAXIAL CABLE				
SPECIFICATIONS						
ITEM		TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION						
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	×	×
MARKING		CONFIRMED VISUALLY.			×	×
	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
△	2	DIS-F-004353		KN. SHIBUYA	HT. YAMAGUCHI	09.12.15
REMARKS (1) INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. (2) OPERATING TEMPERATURE SHOULD BE -55 TO 40°C WHEN HUMIDITY EXCEEDS 80% RH. (3) THE SPECIFICATION IS APPLIED TO THE PRE-ASSEMBLED COMPONENT AND THE CABLE ASSEMBLED PRODUCT BOTH IN DELIVERY AND STORAGE, BEFORE ASSEMBLED TO PCB. (4) THERE MUST NOT BE DEWFALL. (5) IT IS THE MAXIMUM VALUE OF CONNECTOR. CONFIRM THE SPECIFICATION OF THE CABLE.				APPROVED	HS. OKAWA	08.04.18
				CHECKED	HT. YAMAGUCHI	08.04.18
				DESIGNED	KN. SHIBUYA	08.04.17
				DRAWN	KN. SHIBUYA	08.04.17
Unless otherwise specified, refer to JIS-C-5402.						
Note QT:Qualification Test AT:Assurance Test X:Applicable Test				DRAWING NO.		ELC4-157684-00
HRS	SPECIFICATION SHEET			PART NO.	FX16-31P-GND	
	HIROSE ELECTRIC CO., LTD.			CODE NO.	CL575-3312-3-00	△ 1/1