Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	−55 °C TO 85 °C (1)	OPERATING HUMIDITY RANGE	40 TO 80 % MAX (3)
	VOLTAGE	100 V AC	STORAGE TEMPERATURE RANGE	−10 °C TO 60 °C (2)
	CURRENT	0.4 A	STORAGE HUMIDITY RANGE	40 % TO 70 % (2)

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA(DC OR 1000 Hz)	45 mΩ MAX .	×	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV MAX, 1 mA (DC or 1000Hz)	55 mΩ MAX.	×	—
INSULATION RESISTANCE	250 V DC.	100 MΩ MIN.	×	—
VOLTAGE PROOF	300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	50 TIMES INSERTIONS AND EXTRACTIONS.	1) CONTACT RESISTANCE: 55 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
VIBRATION	FREQUENCY 10 TO 55 TO 10 Hz, SINGLE AMPLITUDE: 0.75 mm, AT 2 h FOR 3 DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) CONTACT RESISTANCE: 55 mΩ MAX. 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
SHOCK	490 m/s^2, DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 BOTH AXIAL DIRECTIONS.		×	—
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.	1) CONTACT RESISTANCE : 55 mΩ MAX. 2) INSULATION RESISTANCE: 100 MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE: −55 → +85 °C TIME : 30 → 30 min. UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER:WITHIN 2 TO 3 min)		×	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	1) CONTACT RESISTANCE : 55 mΩ MAX. 2) NO HEAVY CORROSION.	×	—
HYDROGEN SULPHIDE	EXPOSED 3 ppm FOR 96 h. (TEST STANDARD:JEIDA-38)		×	—
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING: PEAK TMP : 250 °C MAX REFLOW TMP: 220 °C MIN FOR 60sec 2) SOLDERING IRONS: 360 °C MAX FOR 5 sec.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINAL.	×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE 240 ± 3 °C FOR IMMERSION DURATION, 3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.	×	—

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					

REMARKS
(1) TEMPERATURE RISE INCLUDED WHEN ENERGIZED.
(2) THIS STORAGE INDICATES A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE THE BOARD MOUNTED.
(3) NON-CONDENSING.
Unless otherwise specified, refer to IEC-60512.

APPROVED	NH.NAKATA	16.11.21
CHECKED	HT.YAMAGUCHI	16.11.21
DESIGNED	MT.ITANO	16.11.21
DRAWN	MT.ITANO	16.11.21

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC-150568-91-00

HRS

SPECIFICATION SHEET — PART NO. FX8-140P-SV(91)

HIROSE ELECTRIC CO., LTD. — CODE NO. CL578-0007-2-91 △0 1/1

FORM HD0011-2-1