Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-40 °C TO 105 °C (NOTE1)	STORAGE TEMPERATURE RANGE	-40 °C TO 105 °C
	VOLTAGE	250 V AC	CURRENT	1 A

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	1A DC.	SIGNAL:30 mΩ MAX, SHIELD:60mΩ MAX.	X	—
CONTACT RESISTANCE MILLIVOLT LEVEL METHOD	20 mV AC MAX, 0.1 mA(DC OR 1000Hz)	SIGNAL:30 mΩ MAX, SHIELD:60mΩ MAX.	X	—
INSULATION RESISTANCE	500 V DC	100 MΩ MIN.	X	—
VOLTAGE PROOF	650 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	—
MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND EXTRACTION FORCES	BY STEEL GAUGE, —.	INSERTION FORCE — N MAX. EXTRACTION FORCE — N MIN.	— —	— —
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X	— —
VIBRATION	FREQUENCY 20 TO 200 Hz, 43.1 m/s^2 AT 3 h FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X X	— — —
SHOCK	FREQUENCY 20 TO 50 Hz, 66.6 m/s^2 AT 1 h.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X X	— — —
LOCK STRENGTH	APPLYING A PULL FORCE THE MATING AXIALLY AT 78.4N MIN.	① DURING APPLYING,MATING COMPLETELY. ② AFTER APPLYING,NO DEFECT OF MATING PARTS.	X X	— —
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 60 °C, 90 ～ 95 %, 500 h.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X X	— — —
RAPID CHANGE OF TEMPERATURE	TEMPERATURE-40→5 TO 35→85→5 TO 35°C TIME 30 → 5 → 30 → 5 min UNDER 1000 CYCLES.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② INSULATION RESISTANCE:100 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X X	— — —
DRY HEAT	EXPOSED AT 105°C, 300 h.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X	— —
COLD	EXPOSED AT -55°C , 120 h.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X X	— —
CORROSION, SALT MIST	EXPOSED IN 5% SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120Mωmax. ② NO HEAVY CORROSION.	X X	— —
RESISTANCE TO SO_2 GAS	EXPOSED IN 500 PPM FOR 8h.	① CONTACT RESISTANCE: SIGNAL:60 mΩ MAX, SHIELD:120mΩ MAX. ② NO HEAVY CORROSION.	X X	— —

	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△0					

REMARK
(NOTE1) INCLUDE THE TEMPERATURE RISING BY CURRENT.

APPROVED	AR. SHIRAI	12. 04. 10
CHECKED	NH. NAKATA	12. 04. 10
DESIGNED	KK. FURUKAWA	12. 04. 09
DRAWN	KK. FURUKAWA	12. 04. 09

Note QT:Qualification Test AT:Assurance Test X:Applicable Test

DRAWING NO. ELC4-167969-00

HRS	SPECIFICATION SHEET	PART NO.	GT17HSK-4S-HU	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL767-0244-0-00 △0	1/1

FORM HD0011-2-1