

Jan.1.2020 Copyright 2020 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				

APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C		STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C				
	VOLTAGE	AC 30 V, DC 42 V							
	CURRENT	1 A		APPLICABLE CABLE	φ 5				

**SPECIFICATIONS**

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×

ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	CONTACT SHALL BE MEASURED AT DC 1 A	30 mΩ MAX.	×	×
	CONTACT SHALL BE MEASURED AT DC — A	— mΩ MAX.	—	—
INSULATION RESISTANCE	100 V DC.	1000 MΩ MIN.	×	×
VOLTAGE PROOF	300 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	×	×

MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND WITHDRAWAL FORCES	BY STEEL GAUGE.	INSERTION AND WITHDRAWAL FORCES: — N MIN	—	—
CONNECTOR INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION AND WITHDRAWAL FORCES: 35 N MAX.	×	—
MECHANICAL OPERATION	1000 TIMES INSERTIONS AND EXTRACTIONS.	CONTACT RESISTANCE: 50 mΩ MAX.	×	—
		— RESISTANCE: — mΩ MAX.	—	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s <sup>2</sup> AT 2 h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—
SHOCK	490 m/s <sup>2</sup> DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	×	—

ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 5 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 50 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → R/T <sup>0</sup> → +85 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES.	① INSULATION RESISTANCE: 1000 MΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION.	×	—
DRY HEAT	EXPOSED AT +85 °C, 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
COLD	EXPOSED AT -55 °C, 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	×	—
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, +380 °C, FOR SOLDERING DURATION, 3 <sub>0</sub> <sup>+1</sup> s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	×	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, +350 °C FOR SOLDERING DURATION, 2 TO 3 s.	WETTING ON SOLDER SURFACE. NO SOLDER CLUSTER.	×	—

REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
NOTE(1) R/T : ROOM TEMPERATURE	H.Kawashima	H.Kawashima	J. Okigawa	M. Sato	
Unless otherwise specified, refer to JIS C 5402.	'05.11.5	'05.11.5	'05.11.05	05.11.05	

Note QT:Qualification Test AT:Assurance Test O:Applicable Test		PART NO. HR25-7TP-8P (72)	
<b>HS</b> HIROSE ELECTRIC CO., LTD.	SPECIFICATION SHEET		
CODE NO. (OLD) CL	DRAWING NO. ELC4-047695-72	CODE NO. CL125-0005-9-72	1/1

