APPLICAB	LE STANDA	RD								
RATING	OPERATING TEMPERATURE	RANGE	−25°C T0 +85	i°C	STORAGE TE RANGE	MPERATURE	-10°C T0 +6	0°C		
					ADDI TOADI E	CARLE	460 70 4			
		— APPLICABLE CABLE φ6.2 TO φ7 SPECIFICATIONS								
		1		JIFICAI		DE	OLUBENENTO	QT	AT	
CONSTRU	CTION	TEST METHOD				REQUIREMENTS				
		VICUALIV	AND BY MEASURING INSTRUMENT.		ACCORDI	NG TO DDAWI	NG	X	Х	
GENERAL EXAMINATION MARKING		CONFIRMED VISUALLY.			ACCORDI	ACCORDING TO DRAWING.			Х	
	CAL CHARAC				<u> </u>					
VIBRATION SHOCK		FREQUENCY 10 TO 55 Hz (1CYC, 5min), SINGLE AMPLITUDE			JDE NO SEPA	NO SEPARTION FROM APPLICABLE CONNECTOR.			_	
		0.75 mm, AT 10 CYC, FOR 3 DIRECTIONS.								
		IN OPPOSITE DIRECTIONS OF EACH 3 DIMENSIONAL AXIS				NO SEPARTION FROM APPLICABLE CONNECTOR.				
	AENITAL CH		NES AT 490 m/s ² DURACTION OF PURISHIPS	JLSE 11 ms.						
	MENTAL CHA			T °C	NO DAMA	CE AND CDAC	V OF DADTS	$\overline{}$	$\overline{}$	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE $-55 \rightarrow R/T^{(1)} \rightarrow +85 \rightarrow R/T$ °C TIME 30 \rightarrow 10 TO 15 \rightarrow 30 \rightarrow 10 TO 15 min UNDER 5 CYCLES.				NO DAMAGE AND CRACK OF PARTS.				
DRY HEAT		EXPOSED AT +85 °C , 96 h.			NO DAMA	NO DAMAGE AND CRACK OF PARTS.				
COLD		EXPOSED AT −55 °C , 96 h.			NO DAMA	NO DAMAGE AND CRACK OF PARTS.			_	
SEALING (2)		EXPOSED AT A DEPTH OF 1 m FOR 0.5 h.			NO WATE	NO WATER PENETRATION INSIDE CONNECTOR.			_	
COUNT DESCRIPTION			ON OF REVISIONS	ı	DESIGNED		CHECKED	D.A	ATE	
A										
REMARK				<u> </u>		APPROVI	ED HY. KOBAYASHI	12 (03. 16	
	T : ROOM TEMPI	ERATURE				CHECKE		_	03. 16	
		E TESTED BY APPLICABLE CONNECTOR.				DESIGNE			18. 03. 16	
Unless oth	nerwise spe	cified. re	ified, refer to IEC 60512.(JIS C 5402)			DRAWN			18. 03. 16	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test					DRAWING NO.		ELC-112684-	ELC-112684-31-00		
LDC	SI	PECIFICATION SHEET			PART NO.		HR30-8P-C (31)	HR30-8P-C (31)		
HS		HIROSE ELECTRIC CO., LTD.				CL130-3003-5-31 🛕 1/1			1/1	
I	THINGOL LLLOTNIO CO., LTD.			,	CODE NO.	0L10U-0U03-0-01 <u>ZU</u> 1/1			''	