

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
RAPID CHANGE OF TEMPERATURE IEC60512-6-11d	5 CYCLES (1 CYCLE=1 HOUR)WITH CONNECTORS ENGAGED. TEMPERATURE:-55 to +85℃	① CONTACT RESISTANCE: AFTER TEST 40 mΩ MAX CHANGE. ② INSULATION RESISTANCE: AFTER TEST 100 MΩ MIN. ③ NO MECHANICAL DAMAGE OR HEAVY CORROSION SHALL OCCUR ON THE PARTS.	×	—	
DRY HEAT IEC60512-6-11i	EXPOSED AT +85 °C FOR 96 HOURS WITH CONNECTORS ENGAGED.		×	—	
COLD IEC60512-6-11j	EXPOSED AT −25 °C FOR 96 HOURS WITH CONNECTORS ENGAGED.		×	—	
DAMP HEAT, STEADY STATE IEC60512-6-11c	EXPOSED AT +40 °C,90 TO 95 % RH, 96 HOURS WITH CONNECTORS ENGAGED.		×	—	
HYDROGEN SULFIDE JEIDA 38	EXPOSED IN 3 PPM HYDROGEN SULFIDE , APPROX. 80% RH,96 HOURS, WITH CONNECTORS ENGAGED.		×	—	
CORROSION SALT MIST (JIS C 5402 7.1)	EXPOSED IN 5±1 % SALT WATER SPRAY , +35±2°C,48 HOURS, WITH CONNECTORS ENGAGED. AFTER THE TEST,THE TEST SAMPLE SHALL BE RINSED WITH WATER AND DRIED AT THE AMBIENT TEMP. FOR 24 HOURS.	NO MECHANICAL DAMAGE OR HEAVY CORROSION SHALL OCCUR ON THE PARTS.	×	—	
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-153563-92-00		
	SPECIFICATION SHEET	PART NO.	DM1B-DSF-PEJ (92)		
	HIROSE ELECTRIC CO., LTD.	CODE NO	CL609-0003-5-92		2/2