	COUNT DESCRIPTION OF REVI			SIONS	BY	CHKD	DATI		COU	лт [DESCR	RIPTION	OF REVI	ISIONS	BY	СНК	D	ATE
A	8	RE-5-20			Y.K.G		18.10.0	1										
	1	RE-5-29			C.Y.H	C.D.H	23.04.2	$^{4}\Delta$										
		OPERATING TEMPERATURE		Δ -40°C ~ +105°C (note1) _{RAI}						RANG							dition)	
RATING				50V [AC(rms) / DC]					ниміс		RATING OR STORAGE /IIDITY RANGE		Relative Humidit 90% MAX(NOT DEV				,	
CURRENT		▲ 0.5A [AC(rms) / D				_	C] (note 2)								=0.3±	:0.03mm)		
			SPECIFICATION								5							
													QT	AT				
CO	NSTR	UCTION																
		VINATION	VISUALLY AND BY MEASURING INSTRUMENT								ACCORDING TO DRAWING						0	0
MARK	-																-	
		CAL CHARAC																
CONTACT RESISTANCE			MATE APPLICABLE FPC/FFC AND APPLY A CURRENT OF AC 20mV MAX (1KHz), 1mA.								50mΩ MAX. INCLUDING FPC/FFC BULK RESISTANCE(L=8mm)						0	0
INSULATION RESISTANCE																	0	0
Voltage proof			AC 150V FOR 1 min.								NO BREAKDOWN						0	0
МЕ																		
MECHANICAL CHARA MECHANICAL OPERATION			20 TIMES INSERTIONS AND EXTRATIONS.								Ω CONTACT RESISTANCE : 50mΩ MAX.							
MECH	in the recipie		20 1110	ES INSEN	1101107					\sim		AMAGE,CR/				ARTS	0	-
VIBRATION			FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, - m/s ² FOR 10 CYCLES IN 3 DIRECTIONS.								 NO ELECTRICAL DISCONTINUITY OF 1μs. CONTACT RESISTANCE : 50mΩ MAX. 						0	-
SHOC	K		981m/s ² DIRECTION OF PULSE 6ms AT 3 TIMES								(a) NO DAMAGE,CRACK AND LOOSENESS OF PARTS						0	-
FPC/FFC RETENSION FORCE			IN 3 DIRECTIONS. MEASURE BY APPLICABLE FPC/FFC.							н	HORIZONTAL DIRECTION : 0.3N X n MIN.					-		
			(THICKNESS OF FPC/FFC SHALL BE t=0.30mm AT INITIAL CONDITION.)								(n : NUMBER OF CONTACTS). <i>(note 3)</i>					0	-	
EN	VIRO	NMENTAL CH	IARA	CTEF	RISTI	CS												
RAPID	CHANG	e of temperature						i → 15	TO 35 °		-	ACT RESIST						
						30 → 2	~3 min			~	-	ATION RES				RTS	0	-
DAMP HEAT (STEADY STATE)			UNDER 5 CYCLES. EXPOSED AT 40±2°C, 90~95 %, 96h.								③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS						0	-
	P HEAT, C		TEMPE	RATURE :	-10 TO													
			HUMIDITY : 90 TO 95% 10 CYCLE, TOTAL 240h.													0	-	
DRY HEAT			EXPOSED AT 105±2°C, 96h.								 CONTACT RESISTANCE : 50mΩ MAX. 						0	-
COLD			EXPOSED AT -40±3°C, 96h.								② NO DAMAGE, CRACK OR LOOSENESS OF PARTS						0	-
CORROSION SALT MIST			EXPOSED AT 35±2°C, 5% SALT WATER SPRAY FOR 96h.								 CONTACT RESISTANCE : 50mΩ MAX. NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR 						0	-
SURPHUR DIOXIDE [JIS C 0090]			EXPOSED AT 40±2°C, RELATIVE HUMIDITY 80±5%, 25±5 PPM FOR 96h.														0	-
HYDROGEN SULPHIDE			EXPOSED AT 40±2℃, RELATIVE HUMIDITY														0	-
[JIS C 0092] RESISTANCE TO SOLDERING HEAT			80±5%, 10 TO 15 PPM FOR 96h. 1) REFLOW SOLDERING :														L.	_
RESISTAINCE TO SOLDERING HEAT			PEAK TMP. 250°C MAX. REFLOW TMP.230°C MIN. FOR 60 sec. 2) SOLDERING IRONS : TMP. 350±5°C FOR 5±1 sec.								 NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS NO DAMAGE OF ELECTRICAL PERFORMANCE 						o	-
SOLDERABILITY		SOLDER DIPPING TEMPERATURE 245±5°C,								A NEW UNIFORM COATING OF SOLDER						1		
			FOR IMMERSION DURATION, 3±0.3 sec.									SHALL COVER A MINIMUM OF 95% OF THE SURFACR BEING IMMERSED.						-
 ▲ (note 1) FOLLOW THE SPECIFICATIONS OF FPC/FFC IF IT'S ALLOWABLE MAXIMUM OPERATING TEMPERATURE IS BELOW 105℃ ▲ (note 2) WHEN THE SAME VALUE OF CURRENT ARE APPLIED TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70% OF THE RATED CURRENT VALUE. ▲ (note 3) THERE'S A CASE WHICH FPC/FFC RETENTION FORCE DOESN'T FULFILL THE VALUE, BECAUSE FPC/FFC SPECIFICATION AFFECTS THE RESULT OF FPC/FFC RETENTION FORCE. 													L					
REN	IARKS							DRAWN			DESIGNED C		CHECKED	HECKED APPROVED			RELEASED	
								B.J KIM		В	B.J KIM D.H		.н сно	о н.	C SON	ıg ∕		
	-98 07		∩ ₽⊏⊏		TO JIS C 5402.				8.03.02		18.03.02 18.0		8.03.02	3.02 18.03.02		02	23.04. DEP	
NOT							TEST	O. ۷۵			TEST						~	
NOTE QT: QUALIFICATION TEST AT: ASSURANCE TEST O: APPLICABLE TEST																		
HIROSE KOREA CO			.,ltd. SPECI			PECII	FICA	ICATION SHI			т	PARIN		38-**S-0.5SV(830)				
CODE NO.(OLD)				DRAWING NO.				CODE NO				I					-,	1 /
CL				ELC4-632306							CL 6537-***-*-830							1