

Jun.1.2022 Copyright 2022 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-40°C TO +85°C	STORAGE TEMPERATURE RANGE	-25°C TO +70°C (AT PACKING)	
	—	—	CHARACTERISTIC IMPEDANCE	(φ2)FIBER CORD	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X	
MARKING	CONFIRMED VISUALLY.		X	X	
OPTICAL CHARACTERISTICS					
INSERTION LOSS	MEASUREMENT AT WAVE LENGTH 1310±30nm(LD)	≤0.7 dB(SM) 1 MATING ≤0.5 dB(GI) WITH 1.5dB-MODESCRAMBLER	X	—	
RETURN LOSS	MEASUREMENT AT WAVE LENGTH 1310±30nm(LD)	≥40 dB(SM) , ≥22 dB(GI)	X	—	
MECHANICAL CHARACTERISTICS					
MATING DURABILITY	5,000 INSERTION AND EXTRACTION.	INSERTION LOSS RANGE : ≤0.3dB NO LOOSENESS, BREAKAGE,CRACKS	X	—	
VIBRATION (JIS E 4031, 5,B)	2 HOURS OF 2 DIRECTION AT AN AMPLITUDE OF 2.3mm WITH THE FREQUENCY SWEEPING CONTINUOUSLY BETWEEN 40 Hz.		X	—	
SHOCK (JIS E 4032,2,A)	3 TIMES AND 2 DIRECTIONS WITH THE ACCELERATION 88m/s ²		X	—	
ENVIRONMENTAL CHARACTERISTICS					
COMPOSITE HUMIDITY CYCLE	HUMIDITY : 90~96% TEMPERATURE : -10~65°C TIME : 240HOURS(10CYCLE)	INSERTION LOSS RANGE : ≤0.3dB NO LOOSENESS, BREAKAGE,CRACKS	X	—	
TEMPERATURE CYCLING	TEMPERATURE : -40~75°C 42CYCLE (TELCORDIA GR-326-CORE)		X	—	
RESISTANCE TO DRY HEAT	TEMPERATURE : 85°C FOR 240HOURS		X	—	
RESISTANCE TO COLD	TEMPERATURE : -40°C FOR 240HOURS		X	—	
SALT MIST	SALT MIST : 5% FOR 1000HOURS	NO HEAVY CORROSION RUIN THE FUNCTION	X	—	
WATER RESISTANCE (MATING)	PUT THE PRODUCT UNDER WATER FOR 1 min. WITH AIR PRESSURE 4.9kPa.	THE VENTILATION VOLUME OF AIR IS 0.25cc or LESS / MINUTE	X	—	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
①					
REMARK			APPROVED	MT. SHIBUTANI	18. 02. 02
Unless otherwise specified, refer to IEC61300 SERIES.			CHECKED	FS. YOSHIDA	18. 02. 02
			DESIGNED	TY. SATO	18. 02. 02
			DRAWN	MK. INOUE	18. 02. 02
			Note QT:Qualification Test AT:Assurance Test X:Applicable Test		
HRS	SPECIFICATION SHEET		PART NO.	MF10B-WRBCH01-0200 (31)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL709-1033-0-31	△ 1/1