

Technical drawing of a mechanical part, likely a cross-section of a shaft or a similar component. The drawing shows a circular cross-section with a central vertical slot. The dimensions are as follows:

- Overall width: 0.9 ± 0.3
- Slot width: 0.9 ± 0.3
- Slot depth: 1.5 ± 0.3
- Slot length: 2 ± 0.3
- Overall height: 0.9 ± 0.3

A(4:1)

[illegible]

Technical drawing of a PCB layout for a 2-Port 3.2V 0.1 component. The drawing shows a rectangular board with a rounded top-left corner. Dimensions are given in millimeters with tolerances: total width 16.1 (+0.1/0), total height 19.4 (+0.1/0), rounded corner radius 8.7 (+0.05/0), and a small gap of 0.2. A dashed line indicates the internal layout area. An arrow points to the 'PC BOARD' label.

RECOMMENDED PANEL CUTOUT(2:1)

Technical drawing of the rear view of a 10-pin D-sub connector. The drawing shows the internal pins and the housing. Dimensions include a total width of 3 ± 0.3 mm and a pin pitch of 1.5 mm. Callouts 4, 3, and 5 point to specific pins.

Technical drawing of a mechanical part with dimensions:

- Overall width: 16.5 ± 0.5
- Width of the top section: 13.1 ± 0.5
- Width of the bottom section: 6.1 ± 0.5
- Overall height: 12.2 ± 0.5
- Height of the bottom section: 15.7 ± 0.5
- Height of the top section: 1.2 ± 0.3

Technical drawing of the GT17VA-8DP-OS (BLACK) component, showing dimensions and labels:

- Overall width: 16.5 + 26.5 = 43.0
- Distance from left edge to center of push button: 13.1
- Push button diameter: 2
- Distance from left edge to center of push button: 15.7
- Distance from left edge to center of push button: 12.2
- Distance from left edge to center of push button: 1.6
- Labels: GT17VA-8DP-OS (BLACK), GT17S-8DS-R, GT17SA-8DS-HU (BLACK), PC BOARD, PANEL, PUSH

MATED CONNECTOR

[illegible]