







Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT




MATED CONNECTORS






RECOMMENDED PCB LAYOUT
(3:1)




RECOMMENDED PANEL CUTOUT



PACKING STYLE
7 TRAYS STACKING.
ODD NUMBER TRAYS AND EVEN NUMBER TRAYS ARE REVERSE DIRECTION.
TOP TRAY IS EMPTY.




1TRAY : 90PCS



NOTES

1. RECOMMENDED REFLOW PROFILE (SEE RIGHT GRAPH)
CYCLE TIME: UP TO 2 CYCLES OF REFLOW SOLDERING ARE POSSIBLE UNDER THE CONDITIONS, PROVIDED THAT THERE IS A RETURN TO NORMAL TEMPERATURE BETWEEN THE FIRST AND SECOND CYCLE.
PEAK TEMPERATURE: 250°C
230°C MIN. FOR 20 TO 40 SECONDS.
PREHEATING AREA 150~180°C FOR 60 TO 120 SECONDS.
2. HAND SOLDERING: 280~300°C, 2SECONDS MAX.
3. CONTACT COPLANARITY: 0.1mm MAX.
4. RECOMMENDED THICKNESS OF PCB: 1.6mm
5. RECOMMENDED THICKNESS OF SOLDERING PASTE: 0.12mm

TEMP. (°C)



2	PA	DARK GRAY		4	BRASS	TIN PLATING			
1	COPPER ALLOY	TIN PLATING		3	BRASS	TIN PLATING			
NO.	MATERIAL	FINISH , REMARKS		NO.	MATERIAL	FINISH , REMARKS			
UNITS mm		SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE	
				0	DIS-T-00018429		KN. YANAGIMOTO	EJ. WAKATSUKI	2023. 06.
			APPROVED : AR. SHIRAI		2017. 03. 14	DRAWING NO.	EDC-353182-30-01		
			CHECKED : TH. MIZUGUCHI		2017. 03. 13	PART NO.	GT32-4DP-1. 5H (30)		
			DESIGNED : TS. KUBOTA		2017. 03. 13	CODE NO.	CL0782-0038-1-30		
DRAWN : TS. KUBOTA		2017. 03. 13							

HIROSE
ELECTRIC
CO., LTD.