


Sep. 1. 2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- ① HAND CRIMPING TOOL, REF. NO. ⑨: HR10A-TC-02(CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING : $\phi 7.0$
 - ② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑦: 2 TO 2.5 N·m.
 - ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑧: 1.27
THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑧: 0.3 TO 0.4N·m.
 - ④ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES TO PREVENT REF. NO. ① AND ⑧ FROM LOOSENING.
 - ⑤ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑦ TO REF. NO. ① IS SHOWN.
 - ⑥ THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0354-00.

| 5 | BRASS | MATTE FINISH NICKEL PLATED | 10 | CR | (BLACK) |
|-----|------------|--|-----|----------|--|
| 4 | BRASS | GOLD PLATING 0.2 μ m min. NICKEL UNDER PLATING 2 μ m min. | 9 | BRASS | |
| 3 | BRASS | | 8 | STEEL | NICKEL PLATING HEXAGON SOCKET SET SCREW M2.6X0.45X3 |
| 2 | POLYAMIDE | (BLACK) UL94V-0 | 7 | BRASS | NICKEL PLATING |
| 1 | ZINC ALLOY | MATTE FINISH NICKEL PLATED | 6 | STEEL | NICKEL PLATING |
| NO. | MATERIAL | FINISH , REMARKS | NO. | MATERIAL | FINISH , REMARKS |

| UNITS mm | SCALE 2 : 1 | COUNT 2 | DESCRIPTION OF REVISIONS DIS-C-00016953 | DESIGNED HT. ZENBA | CHECKED EJ. KUNII | DATE 20240220 |
|----------------------------------|----------------|------------|--|---|----------------------|------------------|
| HIROSE ELECTRIC CO., LTD. | | | APPROVED : MO. SATOH 20051020 CHECKED : EJ. KUNII 20051020 DESIGNED : DS. MATSUNE 20051019 DRAWN : DS. MATSUNE 20051019 | DRAWING NO. EDC4-021366-74 PART NO. HR10A-10P-10P(74) CODE NO. CL0110-0407-3-74 | | |