





- NOTES 1 APPLICABLE CRIMPING CONTACT:HR22-SC-222(CL122-0008-8)
(APPLICABLE WIRE:AWG#24 TO 28, OUTER DIMENSION OF JACKET:φ1.15MAX.)
APPLICABLE CONTACT EXTRACTION TOOL:RP6-SC-TP(CL150-0039-0)
- ② ACROSS FLATS OF HEXAGON SOCKET OF REF.NO.⑫ :1.27.
THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑫ :0.3 TO 0.4N·m.
- ③ THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑦ AND NO.⑪ :2N·m.
- ④ LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF.NO.① AND NO.⑫ FROM LOOSENING.
- 5 ROTATION EXAMPLES OF REF.NO.①, ⑦ AND ⑪ ARE SHOWN.
- 6 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER.
DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

7	BRASS	NICKEL PLATING			
6	PHOSPHOR BRONZE	NICKEL PLATING	13	ACRYLONITRILE BUTADIENE RUBBER	(BLACK)
5	STEEL	NICKEL PLATING	12	STEEL	NICKEL PLATING M2.6X0.45X2
4	BRASS	NICKEL PLATING	11	BRASS	NICKEL PLATING
3	SILICONE RUBBER	(BLACK)	10	BRASS	NICKEL PLATING
2	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	9	SILICONE RUBBER	(BLACK)
1	ZINC ALLOY	NICKEL PLATING	8	SILICONE RUBBER	(BLACK)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.				APPROVED : MO. SATOH	07. 01. 23	DRAWING NO. EDC3-042799-73		
				CHECED : EJ. KUNII	07. 01. 23	PART NO. HR22-12WTPA-20SC(73)		
				DESIGNED : HS. KAWASHIMA	07. 01. 23	CODE NO. CL122-0004-7-73		
				DRAWN : MK. SATO	07. 01. 16			

