


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE, REF. NO. 9 AND 13 : 2N · m. AND LOCTITE 263, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. 9 AND 13 FROM LOOSENING.
 - 2 ACROSS FLATS OF HEXAGON SOCKET OF REF. NO. 14 : 1.27.
AND THE RECOMMENDED CLAMP TORQUE : 0.3 TO 0.4N · m.
 - 3. ONE EXAMPLE OF THE ROTATION OF REF. NO. 1, 9, 13 IS SHOWN.
 - 4. THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE, PLEASE CONFIRM BEFORE THE USE.

8	Phosphor bronze	Nickel plating			
7	Steel	Nickel plating	15	Acrylonitrile-butadiene rubber	(Black)
6	Brass	Nickel plating	14	Steel	Nickel plating
5	Silicone rubber	(Black)	13	Brass	Nickel plating
4	Brass	Silver plating	12	Brass	Nickel plating
3	Brass	Silver plating	11	Silicone rubber	(Black)
2	Polybutylene terephthalate	(Black) UL94V-0	10	Silicone rubber	(Black)
1	Zinc alloy	Silver plating	9	Brass	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT	DESCRIPTION OF REVISIONS	
HIROSE ELECTRIC CO., LTD.		APPROVED	: EJ. KUNII	16. 02. 13	DRAWING NO.
		CHECKED	: EJ. KUNII	16. 02. 13	PART NO.
		DESIGNED	: SJ. SHIMIZU	16. 02. 13	CODE NO.
		DRAWN	: SJ. SHIMIZU	16. 02. 13	
				DESIGNED	
				CHECKED	
				DATE	
				EDC-110496-73-00	
				HR22-12WTPA-20P(73)	
				CL122-0027-2-73	
				1/1	