High Performance, Miniature Circular Connectors

HR22 Series



Product specifications

Features

- Both waterproof and non-waterproof types are available. (Waterproof and nonwaterproof connectors can be mated with each other if needed, but will no longer result in a waterproof connection)
- •Waterproof performance The HR22 waterproof type is IP67 and IP68 rated when mated. IP67 : Left at a water depth of 1 m for 30 minutes
- IP68 : Left at a water depth of 2 m for 14 days
- Both crimp and solder type termination are available. Termination style can be chosen as required by your specific application.
- •The receptacle features a jam nut configuration at the front, which allows for easy panel mounting.
- •The jack connector can also be used as a panel jack.

Dotingo		Rated current	2A		Operating temperature range	-25℃ to +85℃	
Ratings		Rated voltage	100V AC, 140V D	С	Storage temperature range	-10°C to +60°C	
Item		Specifi	cations		Condition	s	
1. Contact res	istance	20mΩ max.		Me	easured at DC 1A		
2. Insulation resistance		1,000MΩ min.		Me	Measured at DC 100V		
3. Withstanding voltage		No flashover or diel	ectric breakdown.	Measured at AC 300V for 1 minute			
4. Vibration resistanceThere shall be no electrical No electrica discontinuity for 10µs or greater.			10 to 500Hz/cycle, amplitude : 0.75mm, acceleration- 98m/s ² 3 axis directions, 2 hours each				
5. Shock resistance		No electrical discon greater.	tinuity for 10 μ s or	Acceleration : 490m/s ² , duration : 11ms, 3 axis directions, 3 times each		11ms, 3 axis directions,	
6. Mating cycles Contact resistance : 20mΩ max.		: 20mΩ max.	100 times				
7. Resistance to water pressure		No water penetratio	n into the connector.		tted connectors left in Water at a urs.	depth of 1.8m for 48	

Materials / Finish

Items	Material	Finish	Remarks
Plated shell	Brass	Niekel plating	
Plated shell	Zinc alloy	- Nickel plating	
Insulator	PBT resin	Black	UL94V-0
Mala contact	Brass (Soldering)		
Male contact	Phosphor bronze (Crimping)	Cilver plating	
Formale contract	Beryllium copper (Soldering)	- Silver plating	
Female contact	Phosphor bronze (Crimping)		
Hood and bushing	Acrylonitrile-butadiene rubber	Black	



Product Number Structure

Refer to the chart below when determining the product specifications from the product number. Please select from the product numbers listed in this catalog when placing orders.


$\frac{\mathsf{HR22}}{\bullet} - \frac{\mathsf{12}}{\diamond} \frac{\mathsf{W}}{\bullet} \frac{\mathsf{T}}{\bullet} \frac{\mathsf{P}}{\bullet} \frac{\mathsf{A}}{\bullet} - \frac{\mathsf{20}}{\diamond} \frac{\mathsf{SC}}{\bullet} \frac{(**)}{\bullet}$

	shell size is the outer diameter of the mating end of the plug.
W : Waterproof	
Blank : Non-wa	terproof
4 Locking mecha	nism
T : Threaded co	oupling type
Shell type	P : Plug
	J : Jack
	R : Receptacle
6 Shell variation :	Variation of the same connector configuration is shown by A, B, C, D
Number of cont	acts
8 Contact form	
P : Male pin	PC : Crimp type male pin
S : Female pin	SC : Crimp type female pin

122-0027-2 73

Plug

Waterproof type




Crimp type	Part No.	HRS No.	RoHS
	HR22-12WTPA-20SC(73)	122-0004-7 73	Yes
Solder type	Part No.	HRS No.	RoHS
	HR22-12WTPA-20S(73)	122-0015-3 73	Yes
		100 0007 0 70	ies

Cable clamping force, rotation force, waterproof performance, and other types of performance may differ depending on the cable type used. Please make sure to verify the suitability of the cable assembly before use or production.

HR22-12WTPA-20P(73)

Non-waterproof type



Crimp type	Part No.	HRS No.	RoHS
	HR22-12TPD-20SC(73)	122-0010-0 73	Yes
	HR22-12TPD-20PC(73)	122-0018-1 73	res


Solder	type
--------	------

r type	Part No.	HRS No.	RoHS
	HR22-12TPD-20S(73)	122-0011-2 73	Yes
	HR22-12TPD-20P(73)	122-0012-5 73	res

Cable clamping force, rotation force, waterproof performance, and other types of performance may differ depending on the cable type used. Please make sure to verify the suitability of the cable assembly before use or production.


Right angle plug

Waterproof type



		(10010001	itativo oxampio,
Crimp type	Part No.	HRS No.	RoHS
	HR22-12WTLP-20PC(31)	122-0064-9 31	Yes
Solder type	Part No.	HRS No.	RoHS
21	HR22-12WTLP-20P(31)	122-0054-5 31	Yes

Cord clamp for use on right-angled plugs



Part No.	HRS No.	А	RoHS
JR13WCC-4(72)	114-2045-0 72	4	
JR13WCC-5(72)	114-2046-3 72	5	Yes
JR13WCC-6(72)	114-2047-6 72	6	

	17	~	
	(Representa	tive e	example)
Part No.	HRS No.	Α	RoHS
JR13WCC-7(72)	114-2048-9 72	7	
JR13WCC-8(72)	114-2049-1 72	8	Yes
JR13WCC-9(72)	114-2050-0 72	9	res

114-2051-372

10

RoHS

Yes

A

24

25.5

Cable clamping force, rotation force, waterproof performance, and other types of performance may differ depending on the cable type used. Please make sure to verify the suitability of the cable assembly before use or production.

JR13WCC-10(72)

HRS No.

122-0014-073

122-0013-873


Receptacle

Waterproof / Non-waterproof combined use type

Part No.

HR22-12WTRA-20S(73)


HR22-12WTRA-20P(73)



Solder type

(Applicable cable dia.)


Jack



Crimp type	Part No.	HRS No.	RoHS
	HR22-12WTJA-20PC(73)	122-0006-2 73	Yes

Cable clamping force, rotation force, waterproof performance, and other types of performance may differ depending on the cable type used. Please make sure to verify the suitability of the cable assembly before use or production.

Non-waterproof type





Solder type	Part No.	HRS No.	RoHS
	HR22-12TJD-20S(73)	122-0023-1 73	Yes
	HR22-12TJD-20P(73)	122-0022-9 73	res


Cable clamping force, rotation force, waterproof performance, and other types of performance may differ depending on the cable type used. Please make sure to verify the suitability of the cable assembly before use or production.

Contact

Male contact







Male contact


Item	Part No.	HRS No.	Applicable cable	Packaging	RoHS
Loose contact	HR22-PC-122	122-0017-9	24 to 28 AWG	100 pcs/pack	Yes
Reel contact	HR22-PC-222	122-0009-0	Insulation diameter ϕ 1.15MAX	10,000 pcs/reel	

Female contact


Item	Part No.	HRS No.	Applicable cable	Packaging	RoHS
Loose contact	HR22-SC-122	122-0016-6	24 to 28 AWG	100 pcs/pack	Yes
Reel contact	HR22-SC-222	122-0008-8	Insulation diameter ϕ 1.15MAX	10,000 pcs/reel	


Applicable tools

Item		Part No.	HRS No.	Applicable terminal	Applicable wire
Manual crimping tool		HR22-TA2428HC	150-0200-4	HR22-PC-122 HR22-SC-122	24 to 28 AWG Insulation diameter \$\phi1.15MAX\$
Automatic crimping tool	Machine body	CM-105C	901-0001-0		
	Applicator	AP105-HR22-2	901-2023-7	HR22-PC-222 HR22-SC-222	24 to 28 AWG Insulation diameter ϕ 1.15MAX
Cable crimping tool		HR10A-TC-04	150-0058-5		¢8.5
Extractor		RP6-SC-TP	150-0039-0		
Cable termination tool		HR22-12P-T01	150-0075-4		Plug connector use



Panel mounting dimensions





Notes: The above figure shows the pin allocation viewed from the engagement side.

Precautions

- 1. Switch off the power of the circuit before disconnecting or plugging-in the connectors.
- 2. Use connectors with socket contacts at the power side of the circuit.
- 3. Make sure that the coupling is in completely cocked position.
- 4. The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.
- 5. This product uses silver plated contacts. Please be aware that silver easily reacts to sulfur gases, causing discoloration or degradation when exposed to certain environmental conditions as shown below. These conditions include areas with:
 - · Dusty site
 - Area or location with a high density of sulfur dioxide gas, hydrogen sulfide gas, nitrogen dioxide gas, or other gas (Emission gases from vehicles and factories, etc.)
 - · Highly fluctuating temperatures, such as close to a heating apparatus.

In addition, it is recommended to store the products in their original packaging or similar state in order to prevent discoloration.

• Temperature : -10 to +60°C, relative humidity : 80% or lower (An environment where temperature and relative humidity are constant and there is little temperature variation.)

Please use the products within six months after delivery. (If the storage period has expired, please examine the connectors and solder cups for corrosion and/or tarnish.)



MEMO:

HIROSE ELECTRIC CO.,LTD.

2-6-3,Nakagawa Chuoh,Tsuzuki-Ku,Yokohama-Shi 224-8540,JAPAN https://www.hirose.com/

8 RS The characteristics and the specifications contained herein are for reference purpose. Please refer to the latest customer drawings prior to use. The contents of this catalog are current as of date of 06/2021. Contents are subject to change without notice for the purpose of improvements.